




## TFER-5/8-X-STK Product Details

 [Share](#)  [Print](#)  [Email](#)



TFER-5/8-X-STK

TE Internal Number: 5960062001

 [Active](#)

### Heat Shrink Tubing

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Heat Shrinkable Tubing
- Product Name = TFER
- Product Source = U.K.
- Flexible
- Thin Wall Style

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Heat Shrinkable Tubing
- Material = Polytetrafluorethylene (PTFE)
- Color = Clear

#### Electrical Characteristics:

- Product Source = U.K.
- [Expanded ID, Min. \(mm \[in\]\)](#) = 15.90 [0.625]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 4.50 [0.177]
- Product Use = Couplings, Hydraulic Hose
- [Cut Length \(mm \[in\]\)](#) = 1220.00 [48.068]

#### Body Features:

- [Product Name](#) = TFER
- Pliancy = Flexible
- [Wall Style](#) = Thin
- [Wall Type](#) = Single
- [Shrink Ratio](#) = 3.2:1
- Fluid Type = Brake Fluid, Chemicals/Solvents, Water
- Resistant To = Fluids, Mechanical Damage
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 0.30 [0.012]

#### Housing Features:

- Material Systems = No
- Flammability Rating Type = Flame-Retardant

#### Industry Standards:

- Government/Industry Qualification = No
- UL Rating = None
- CSA Certified = No
- Approved Standards = BS 4G-198 Part 4 Type 21A, DEF Std 59-97 Type 5B, SAE AMS-DTL-23053/12
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Environmental:

- Fluid Resistance = Splash Protection
- [Operating Temperature \(°C\)](#) = -67 - +250

#### Conditions for Usage:

- Full Recovery Temperature (°C) = 340
- Shrink Temperature, Min. (°C) = 340
- High Temperature Compatible = Yes

#### Operation/Application:

- Application = Insulation and Protection
- Emission Free = No

#### Packaging Features:

- Packaging Method = Stick

#### Other:

- Brand = Raychem

### Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

### Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

