







(B) SEE NOTE 5



TYPICAL SCHEMATIC

NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. MATES WITH: 50 POSITION FEMALE D-SUB
- (B) 4. END CAP MOUNT SCREW TORQUE: 0.5 N-m (4.4 lbf-in) MINIMUM
0.6 N-m (5.3 lbf-in) MAXIMUM
- (B) 5. TERMINAL BLOCK SCREW TORQUE: 0.8 N-m (7.1 lbf-in)
6. ASSEMBLY ROHS COMPLIANCE NOT REQUIRED.



3	2	DIN RAIL ADAPTOR UNIT	THERMOPLASTIC	BLACK
2	1	MALE D-SUB TO 5.08 FIXED, PC BOARD ASSY.	-	-
1	1	5.08 FIXED, DUAL LEVEL BTS	SEE SD-39880-006	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

ADD SCREW TORQUE EC NO: ETC2007-0331 DRWN:CLYORK 2007/03/12 CHKD: JMACNEIL 2007/03/14 APPR: JMACNEIL 2007/03/15				DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 1:1		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		
▽=0			mm		INCH	DRAWN BY C. YORK		DATE 2004/11/15		TITLE DIN RAIL INTERFACE MOD, 50 POSITION MALE D-SUB TO 5.08MM 2 LEV. FIXED						
◇=0		4 PLACES	± ---		± ---	CHECKED BY R. STONE		DATE 2004/11/16								
		3 PLACES	± ---		± .005	APPROVED BY G. ROBERTSON		DATE 2004/11/16								
		2 PLACES	± 0.13		± .01	MOLEX MOLEX INCORPORATED										
		1 PLACE	± 0.3		± ---											
		ANGULAR ± 2 °			MATERIAL NO. 39170-2050				DOCUMENT NO. SD-39170-010				SHEET NO. 1 OF 1			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											