

5

4

3

2

1

Edge mark on first conductor

81,28

1,27 ±0,08

AWG 28/7


Grey

0,89 ±0,08

Cross section at flat

0,64 ±0,18

63 x 1,27 = 80,01 ±0,38



Wire ————— Tinned copper

Gauge ————— AWG 28/7 0,089 mm²

Voltage rating ————— 300 Vr.m.s

Current rating ————— 1,3 A at 10°C rise
above ambient

Capacity unbalanced ————— 78,7 pF/m nominal at 1MHz

Impedance unbalanced ————— 75 Ω nominal

Conductor resistance ————— 225 mΩ/m

Propagation delay ————— 5,25 ns/m nominal

Insulation material ————— PVC

Temperature rating ————— -20°C (operating) | to +105°C
-30°C (static)

Insulation resistance ————— 10 000 MΩ/km


Approvals ————— UL Listed PLCC2-CL2
CSA Certified AWM FT-1

Slit section

∅ 12,70

38,10 19,5
57,15

- ① : Flat cable, AWG 28/7
- ② : Clear polyester
- ③ : Outer jacket: black PVC

				Det.	Name	 All Dim. in mm Orig. Size DIN A 4	SEK 18 round flat cable, not shielded, 64 poles	Maßstab/ Scale
				Detail.	25/10/05 JMDR			
				Insp.				
EC01911	25/05/10	SC		Stand.			TB 09 18 064 70XX	Blatt/ Page 2 / 2
34612	20/09/07	PK						
33247	25/10/05	JMDR						

09 18 064 7011	100 m (328 feet)
09 18 064 7008	30,48 m (100 feet)
Part number	Length per reel

HARTING EURL
F-95972 Paris

Sub.