

# MicroStrobe

- Simple to install
- High intensity Xenon flash
- Compact one-piece housing
- Push-in rapid connection
- Standard 22mm hole pattern
- Fully weatherproof to IP65 (front)
- Minimum 5 million flashes
- 5 lens colours

## Xenon Flashing Panel Mount Indicators




# MiniStrobe

- 12 or 24 volts
- Intense Xenon flash
- Fully weatherproof to IP67
- 5 lens colours

### Applications Include:

Security  
Industrial  
Door Entry Controls  
Warden Controlled Monitors  
Alarm Panels

## Integrated Xenon Beacons



*The Ministrobe comprises  
a drive module and Xenon tube  
mounted in a neat weatherproof housing.*

Both the Microstrobe and the Ministrobe are compact and reliable Xenon flashing devices to be integrated in a wide range of OEM applications. They offer an effective and attractive solution when quality and reliability cannot be compromised.

# MicroStrobe *Xenon Flashing Panel Mount Indicators*

## technical specification

| MODEL         | VOLTAGE RANGE         | POWER OUTPUT | CURRENT CONSUMPTION (mA) |         |         |         | FLASH RATE NOMINAL | WEIGHT (Gms) |
|---------------|-----------------------|--------------|--------------------------|---------|---------|---------|--------------------|--------------|
|               |                       |              | @10v                     | @12v    | @24v    | @100v   |                    |              |
| XP2XMV/1      | 10-100Vdc<br>20-72Vac | 1W           | 70<br>-                  | 72<br>- | 56<br>- | 22<br>- | 120/min            | 53           |
| XP2X110-130/1 | 110-130Vac            | 1W           | -                        | -       | -       | -       | 120/min            | 53           |
| XP2X230/1     | 230Vac                | 1W           | -                        | -       | -       | -       | 120/min            | 53           |

Strobe unit weatherproof to IP65 when installed. Operating temperatures: -20°C to +50°C.

High Voltage transient and polarity reversal protection fitted.

CE complies with EMC directive 89/336/EEC and Low Voltage Directive 73/23/EEC, where appropriate.

## dimensions

114mm x 44mm x 30mm overall  
depth behind panel 89mm

**12 months guarantee** C E

## materials and lens colours

Polycarbonate Lens





# MiniStrobe *Integrated Xenon Beacons*

## technical specification

The Ministrobe comprises 2 assemblies - a drive module and a Xenon lamp unit. The drive module is available in either 12V or 24V.

| MODEL    | VOLTAGE | POWER OUTPUT | CURRENT CONSUMPTION (mA) | FLASH RATE NOMINAL | WEIGHT (Gms) |
|----------|---------|--------------|--------------------------|--------------------|--------------|
| MS1X12/1 | 12V     | 1W           | 115                      | 60/min             | 65           |
| MS1X24/1 | 24V     | 1W           | 55                       | 60/min             | 65           |

12V 0.5W version available to special order. Strobe unit weatherproof to IP67 when installed. Operating temperatures: -20°C to +50°C.



## dimensions

Drive Module: 62mm x 33mm x 22mm

Lamp Unit: 79mm x 31mm x 21mm

## materials and lens colours

High Impact Acrylic Lens. Synthetic Rubber Base



**12 months guarantee**

 **delta design**  
a division of NICOTECH Limited

Primrose Hill, Kings Langley,  
Herts WD4 8HD, England.

Tel: (U.K.) 01923 269522  
(Int.) +44 1923 269522

Fax: (U.K.) 01923 260167  
(Int.) +44 1923 260167

E-mail: [sales@deltadesign.co.uk](mailto:sales@deltadesign.co.uk)  
Web: <http://www.deltadesign.co.uk>



BS EN ISO 9001  
Certificate No. 2272

**Your Delta Design distributor:**

*All specifications are nominal and subject to change without notice.*