

AC-AC UL/cUL ADAPTOR AC 16V 900mA

A. Electrical specifications

1. Input voltage: AC 120V $\pm 10\%$ 60Hz ± 0.5 Hz
2. Output voltage and current: AC 16V at 900mA

V_{in}	100% Load
108	13.0VAC MIN
120	15.5-16.5VAC
132	-

No Load

19.0VAC MAX
21.0VAC MAX

NOTE: Specification applies after 10 minutes warm-up with full load and at any operating temperature.

3. Operating temperature: -10°C to $+40^{\circ}\text{C}$
4. Storage temperature: -20°C to $+85^{\circ}\text{C}$
5. Operating and Storage Humidity: 0 to 95% without condensation
6. Withstand voltage: AC 1000Vrms 1 minute @ input to output


B. Typical performance data test Condition:
 $T_a = +25^{\circ}\text{C}$ measured after 10 minute warm-up with input at 120V 60Hz

C. Safety agencies


UL and cUL File No. E218172

D. Nameplate: Information is as follows:

Metallic letters on a black background




TYPICAL PERFORMANCE CHART



E. Mechanical Specifications

All dimensions shown are nominal unless otherwise specified



PREPARED BY:

K. BRENNAN

ENGINEER:

M. PITCHAI

QUALITY CONTROL:

T. CLEM

APPROVED:

Y. SEKIGUCHI

DWG CONTROL NO.
P-A7-13044
ACAD\PS\A7130441.DWG

REV
A

UL/cUL AC 16V 900mA
POWER SUPPLY

CONTENTS OF THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT
PRIOR NOTICE

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(951) 699-1270 FAX 9516769482

830AS16090

MODEL SPECIFICATION

DIM: mm(In) SCL: NONE SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.