

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20







COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-18-016962	29OCT2018	SC	BH



NOTE;

1. APPLICABLE CONTACT P/N

-TAB CONTACT: 177917-□ (AWG#16-#20)
177916-□ (AWG#22-#26)

2. MATING CONN. P/N

-PLUG HSG: 2005247-□
-REC CONTACT: 177915-□ (AWG#16-#20)
177914-□ (AWG#22-#26)

3. APPLICABLE DOUBLE LOCK PLATE:

177918-1(V-0) / □-368590-1(V-2, GWT)

*IT SHOULD BE USED CERTAINLY WHEN CABLE ASS'Y

4. GENERAL TOLERANCES: ±0.3


5. MATERIAL: PA66, UL94V-0, GWIT 775°C, GWEPT 750°C,
CTI 250V AND BALL PRESSURE 125°C

6. MIN. THICKNESS OF INSULATING WALL

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

5

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

-

DWN

SC KIM

CHK

BW KANG

APVD

JK SONG

PRODUCT SPEC

108-61106

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

PDL 2P CAP HSG 3.96mm F/H (GWT)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-2005248

SCALE

4:1

SHEET

OF

REV

B