




- 1 NYLON, UL 94V-0 RATED, RED.
- 2 BRASS PER ASTM B36.
- 3 3.81um [.000150] MIN TIN OVER 2.54um [.000100] MIN COPPER.
- 4 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 5 SELECTIVELY LOADED CONTACTS IN POSITIONS 1 THRU 5, 7 THRU 12.
- 6 3.81um [.000150] MIN TIN OVER 2.54um [.000100] MIN COPPER.

- 7 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8 SUPERSEDED BY 1-207120-2

6	YES	5	1-207120-2
7	NO		1-207120-1
6	NO		1-207120-0
6	YES		207120-9
7	YES		207120-8
3	YES	5	207120-7
4	NO		207120-4
4	YES		207120-3
3	NO		207120-2
3	YES		207120-1
CONTACT FINISH		MOUNTING TABS	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			
DIMENSIONS: mm [INCHES]		DWN L.SIPE 03/11/92	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R.STONE 3-17-92	
0 PLC ± -		APVD -	
1 PLC ± -		PRODUCT SPEC	
2 PLC ± 0.25 [.010]		108-10033	
3 PLC ± -		APPLICATION SPEC	
4 PLC ± -		-	
ANGLES ± -		-	
FINISH		WEIGHT -	
MATERIAL HOUSING: 1		CONTACT: SEE TABLE	
CUSTOMER DRAWING		SCALE 4:1	
		SHEET 1 OF 1	
		REV S2	