


## Power Feed Block




|                                 |                                                                                   |
|---------------------------------|-----------------------------------------------------------------------------------|
| Type/Cat. No.                   | P95UB                                                                             |
| Electrical Ratings              | 200A/ 480VAC                                                                      |
| Terminal Site Acceptability     | 1-4/0 AWG (50-120mm <sup>2</sup> )                                                |
| Recommended/<br>Required Torque | 19.5Nm (175lb. in.)                                                               |
| Material of Lug/ Terminal       | Brass                                                                             |
| Insulation Material             | Polyamid                                                                          |
| For use with                    | UL1077/508 18 and 25mm <sup>2</sup><br>3 phase busbars<br>(standard spacing only) |

## Dimensions



## Assembly Instructions



## Miscellaneous Accessories

### End Caps



Type/Cat. No: **18/25CAP3P**  
For use with: 18/25mm<sup>2</sup> 2&3 phase Busbar

### Insulation Caps



Type/Cat. No: **BRS5** (5 per strip)  
For use with: 18/25mm<sup>2</sup> 1-3 phase Busbar

NOTE: The Power Feed Block uses the space of 5 Pins of the standard spacing Busbar (see drawing below). Phase 1 connects to Pin 1, Phase 2 to Pin 3 and Phase 3 to Pin 5. Pin 2 and 4 are not in use. Pin 6 should be covered with an insulation cap if phase sequence stays the same. Therefore, the Power Feed Block covers 6 pins to connect to the three phases.

