



AFCI

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.






Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



SECTION
A-A SCALE 2:1



NOTES

1. MATERIAL: HOUSING: HIGH TEMPERATURE PLASTIC, UL94V-0 CONTACT: COPPER ALLOY HOLD DOWN: COPPER ALLOY
2. FINISH: 1.27um MIN NICKEL UNDERPLATE OVERALL, 2.54um MIN TIN (LEAD-FREE) ON SOLDER TAIL, 0.76um MIN GOLD IN CONTACT AREA
3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRARED OR VAPOR PHASE REFLOW OVEN
5. CONTACT WIPE: 2.07 MIN FDR SIGNAL AND 2.52 MIN FDR GROUND

SCALE 2:1

RECOMMENDED PCB LAYOUT
(ALL TOLERANCES ARE ± 0.05)

4 LANE VERTICAL TH HEADER	title	
	no 10044625	Rev. B
catalog no	CUSTOMER	sheet 2 of 2