





DO NOT SCALE

DIMENSIONS IN MM.

SECTION X-X
SCALE: 10:1

SECTION Y-Y

WIRE RANGE: 0.2 TO 0.5 mm²

INSULATION RANGE: 1.6 TO 1.8 mm DIA.

THIN WALLED CABLE TO BE USED

PRODUCT SPEC. 108-3069

APPLICATION SPEC. 114-3040

H/TOOL PN.525317-6 (FOR 0.5 mm² WIRES)SEALED APPLICATIONS ONLY.

PRE-TINNED BRASS				MADE FROM STRIP PN.345808-1				345949-1					
FINISH				MATERIAL				PART NUMBER					
CUSTOMER DWG FOR REFERENCE ONLY				©COPYRIGHT 1991 BY AMP OF GREAT BRITAIN LTD. ALL INTERNATIONAL RIGHTS RESERVED.ALL PRODUCTS MAY BE COVERED BY BRITISH AND FOREIGN PATENTS AND/OR PATENTS PENDING.				RELEASED FOR PUBLICATION 09 JUL 1991					
-	-	-	-	TOLERANCES UNLESS OTHERWISE STATED DEC ± 0.5 ANGLES ± 1°				DR. R.J.S. 9.7.9					
-	-	-	-					CH. H.McG.		APP. J.P.			
-	-	-	-					AMP of Great Britain Ltd.				TERMINAL HOUSE STANNORE MIDDX.	
-	-	-	-										
A	ES00-0041-01		16.02.01	NAME LOOSE PIECE .070" RECEPTACLE ECONOSEAL 3 L.C. (SEALED)									
2	WIRE BARREL WAS PRE-FORMED	C5882	12.11.91										
1	PRELIM. ISSUE	-	9.7.91	SCALE	LOC	SIZE	DWG.No.	REV	SHEET				
REV	APPROVED	ECN	DATE	5/1	E	A3	C345949	A	1/1				