





DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS
 RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

LOC	DIST	REVISIONS	DATE	APPD
AA	22			
		REVIS		
		DESCRIPTION		
		B REVISED: ECN AA-8120	3-24-92	635



2



- 1 MATERIAL: HOUSING-PBT POLYESTER, BLACK. TERMINAL-.0138 THICK PHOS BRONZE PLATED WITH .000500 THICK HARD GOLD IN LOCALIZED GOLD PLATE AREA AND .000080 THICK TIN-LEAD IN SOLDER AREA OVER .000050 THICK NICKEL UNDERPLATE.
- 2 CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68 AND REA BULLETIN 345-81, PE-76 SPECIFICATION FOR MODULAR TELEPHONE HARDWARE.
3. FOR APPLICATION INFORMATION SEE AMP SPECIFICATION 114-2048.
4. FOR PERFORMANCE REQUIREMENTS SEE AMP SPECIFICATION 108-1163.
5. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 6 BULK PACKAGED IN A TRAY.
- 7 PACKAGED 30 PER TUBE.

556416 -2
556416 -1
PACKAGED PART NO

UNLESS OTHERWISE SPECIFIED
 DIMENSIONS ARE IN INCHES
 TOLERANCES ON
 2 PL DEC ±
 3 PL DEC ±
 ANGLES ±

DR *Stinson* 3-8-89
 CHK *St. Fox* 3-13-89
 APPD *Gene Reed* 3-13-89
 APPD *D. J. L. L. L.* 3-13-89
 PRODUCT SPEC

AMP | AMP INCORPORATED
 Harrisburg, Pa. 17105

NAME
 MODULAR JACK ASSEMBLY,
 TOP ENTRY, 8 POSITION,
 FLANGELESS, W/O PANEL STOPS

MATERIAL	FINISH	APPLICATION SPEC	SIZE	FSCM NO	DRAWING NO
1	1		C	00779	556416
WEIGHT	SCALE	4:1	SHEET	1 of 1	

CUSTOMER DRAWING