








TABLE-1



APPLICABLE CABLE WIRE		
	CONDUCTOR	AWG#24 STRANDED WIRE ~ AWG#27 STRANDED WIRE
	INSULATOR DIAMETER	($\phi 0.9 \sim \phi 1.0$)
	JACKET DIAMETER	($\phi 5.8 \sim \phi 6.0$)



- NOTES
- 1> APPLICABLE CABLE IS SHOWN IN TABLE-1
 - 2> PLEASE USE ACCESSORY AS A GUIDE PLATE AND ASSEMBLE CONNECTOR WITH CABLE INSERTING ACCESSORY INTO CONNECTOR.
 3. () INDICATES THE REFERENCE DIMENSIONS.
 4. TO SATISFY CAT6a PERFORMANCE, PREASE ASSEMBLE ACCORDING TO HRS INSTRUCTION. (ETAD-E2847)
 - 5> COLORS ARE DIFFERENT DEPENDING ON THE SPECIFICATION NUMBER.

CL222-2862-9-**
TM21P-88P(**)

COVER(SOLD SEPARATEIL)MATED



2	PHOSPHOR BRONZE	CONTACT:GOLD PLATING 1.27 μ m MIN LEAD: GOLD PLATING 0.03 μ m MIN UNDER: NICKEL PLATING 2 μ m MIN			
1	PHOSPHOR BRONZE	CONTACT:GOLD PLATING 1.27 μ m MIN LEAD: GOLD PLATING 0.03 μ m MIN UNDER: NICKEL PLATING 2 μ m MIN	5	POLYCARBONATE	(YELLOW)UL94V-2
			4	POLYCARBONATE	(YELLOW)UL94V-2
			3	STAINLESS STEEL	OVER:NICKEL PLATING 0.5 μ m MIN
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT		DESCRIPTION OF REVISIONS
DESIGNED		CHECKED		DATE	
APPROVED : YH. ENAMI		09. 01. 26		DRAWING NO. EDC3-126868-00	
CHECKED : YH. ENAMI		09. 01. 26		PART NO. TM31P-TM-88P	
DESIGNED : MT. ITANO		09. 01. 26		CODE NO. CL222-4626-7-00	
DRAWN : MT. ITANO		09. 01. 26		1/1	