


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



PRODUCT NO
73481-XXX



RECOMMENDED HOLE PATTERN
COMPONENT SIDE

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	Electronics www.fciconnect.com		
ltr	ecr no	dr	date	linear	angles		title	product family	code
C				.XX±.13	0° ±2°	projection	MONOBLOCK HEADER ASSY	5 ROW, STB, 72 mm	213
				.XXX±.051		MM	size	dwg no	sheet
				dr M. FETROW 12/15/97		scale	A4	73481	2 of
				engr C. PENDLETON 12/15/97		2.125:1			
				chr R. DOUTRICH 4/22/98					
				appd R. DOUTRICH 4/22/98					
sheet index	revision sheet								

cage code
22526

ACAD

PDM: Rev:D


STATUS: Released

Printed: Sep 24, 2003

PRODUCT NUMBER	DIM. B	ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
73481-X01	2.65	E	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
		D	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	
		C	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	
		B	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	
		A	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
			SM				SM				SM				SM				SM				GM															
73481-X02	2.65	E	-	-	-	-	-	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
		D	-	-	-	-	-	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	
		C	-	-	-	-	-	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	
		B	-	-	-	-	-	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	
		A	-	-	-	-	-	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
			GM				SM				SM				SM				SM				SM															
73481-X03	2.65	E	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
		D	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11		
		C	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12		
		B	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11		
		A	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
			SM				SM				SM				SM				SM				HM															
73481-X04	2.65	E	-	-	-	-	-	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
		D	-	-	-	-	-	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	
		C	-	-	-	-	-	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	
		B	-	-	-	-	-	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	
		A	-	-	-	-	-	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
			HM				SM				SM				SM				SM				SM															
73481-X05	2.29	E	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
		D	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11		
		C	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12		
		B	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11		
		A	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
			SM				SM				SM				SM				SM				GM															
73481-X06	2.29	E	-	-	-	-	-	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
		D	-	-	-	-	-	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	
		C	-	-	-	-	-	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	
		B	-	-	-	-	-	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	11	
		A	-	-	-	-	-	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	
			GM				SM				SM				SM				SM				SM															

PLATING IN CONTACT AREA		
PLATING CODE		
-1YY	0.8µm GOLD	1.3µm Ni MIN
-2YY	2.0µm GOLD	1.3µm Ni MIN
-3YY	1.3µm GOLD	1.3µm Ni MIN
-9YY	0.8µm GXT	1.3µm Ni MIN

SIGNAL PIN KEY	
CODE	DIM "A"
09	5.00
10	5.75
11	6.50
12	7.25
-	NOT LOADED

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		 Electronics www.fciconnect.com	
litr	ecn no	dr	date	linear	projection	title	
C						MONOBLOCK HEADER ASSY	
				angles		5 ROW, STB, 72 mm	
				dr	M. PETROW	12/15/97	product family
				engr	C. PENDLETON	12/15/97	METRAL (tm)
				chr	R. DOUTRICH	4/22/98	code
				appd	R. DOUTRICH	4/22/98	size
sheet index	revision sheet						dwg no
							73481
			</				



PLATING IN CONTACT AREA			
PLATING CODE			
-1YY	0.8µm	GOLD	1.3µm Ni MIN
-2YY	2.0µm	GOLD	1.3µm Ni MIN
-3YY	1.3µm	GOLD	1.3µm Ni MIN
-9YY	0.8µm	GXT	1.3µm Ni MIN

SIGNAL PIN KEY	
CODE	DIM "A"
02	5.75
03	6.50
04	7.25
-	NOT LOADED

PRODUCT NUMBER	DIM. B	ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36
73481-X07	4.25	E	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02
		D	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03
		C	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04
		B	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03
		A	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02
			SM				SM				SM				SM				SM				SM				SM				GM							
73481-X08	4.25	E	-	-	-	-	-	-	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02
		D	-	-	-	-	-	-	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03
		C	-	-	-	-	-	-	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04	04
		B	-	-	-	-	-	-	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03	03
		A	-	-	-	-	-	-	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02	02
			GM				SM				SM				SM				SM				SM				SM				SM							

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		Electronics www.fciconnect.com	
litr	ecn no	dr	date	linear	.X±.3	projection	title
D					.XX±.13		MONOBLOCK HEADER ASSY
				angles	.XXX±.051		5 ROW, STB, 72 mm
					0° ±2'	MM	product family
				dr	T. BREWBAKER 10/27/99		METRAL (tm)
				enfr	D. McCLUNE 10/27/99	1.5:1	code
				chr	D. McCLUNE 10/27/99		213
				appd	D. McCLUNE 10/27/99	size	sheet
sheet index	revision	sheet				A4	4 of
						73481	
						cage code	
						22526	