


Item no.: 233-512
Product description: PCB terminal strip 2 solder pins/pole 12-pole Pin spacing 2.54 mm / 0.1 in with push-button



Produkt kann von Bild abweichen / product may differ

Packing unit 140 4*35 pieces

RoHS compliant

Product group	4 (Printed Circuit)
Weight	4.75 g
Color	orange
No. of connection Points	12
No. of potentials	12
pole count	12
Height	15.5 mm
Height	0.61 in
Width	32.78 mm
Width	1.291 in
Depth	13.9 mm
Depth	0.547 in
Pin spacing from	2.54 mm
Pin spacing from	0.1 in
Rating based on	IEC/EN 60664-1
Overvoltage category EN I	III
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV

Current intensity EN	6 A
Overvoltage category EN II	II
Pollution degree	2

Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Overvoltage category EN III	III
Degree of pollution	3
Rated voltage EN	63 V
Rated surge voltage	2.5 kV
Nominal current	6 A
Connection method	CAGE CLAMP®CONNECTION
Cross section [mm²]	0.08 - 0.5 mm²
Wiring method	solid
Cross section [mm²]	0.08 - 0.5 mm²
Wiring method	fine-stranded
Cross section [mm²]	0 - 0.25 mm²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section [mm²]	0 - 0.25 mm²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	28 - 20 AWG
Strip length from	5 mm
Strip length to	6 mm
Strip length from [inch]	0.2 in
Strip length up to [inch]	0.24 in



Conductor entry angle to the PCB (degrees)	30 °
Solder pin length [mm]	4 mm
Solder pin width A [mm]	0.5 mm
Solder pin width B [mm]	0.75 mm
Diameter of drilled hole [mm]	1.1 mm
Tolerance of drilled hole diameter [mm]	0.1 mm
Material group	I
Insulating material	PA 6.6
Temperature stability	-60 °C to +105 °C
Flammability category, based on UL 94	0V
Clamping spring material	Nickel-chromium spring steel (CrNi)
Contact material	Electrolytic copper (Ecu)
Contact plating	tin-plated



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
233-512	ABS	04-HG469925/1-PDA	250	4	0,08-0,5
233-512	BV	11915/A0	250	6	0,08-0,5
233-512	CSA	154112-1465035	150	4	28-20
233-512	DNV	E-9215	250	4	0,08-0,5
233-512	GL	17296-00HH	250	4	0,08-0,5
233-512	KEMA	90.6212.01/02	250	6	0,08-0,5
233-512	RMR	11130002	250	4	0,08-0,5
233-512	UR	E45172	150	4	18-28

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected