

EZ-LIGHT™ Traffic Light

Indicators for signaling applications

Features



- Preamsembled indicators for signaling and traffic control
- Intense levels of light output for outdoor applications
- Sun shield included
- Controlled field of view for signage and narrow lane use
- Rugged, cost-effective and easy-to-install
- Compact devices are completely self-contained — no controller needed
- One, two or three indicators
- Immune to EMI and RFI interference
- Choose NPN or PNP input, depending on model
- Choose 15 to 30V dc or 85-130V ac operation

Models

Models*	Indicators	LED Function**	Inputs	Construction	Connection	
SP150GPQ	1	1 Color: Green	PNP/ NPN selectable	Flat or DIN-mount polycarbonate	4-pin Euro Integral QD	
SP150RPQ		1 Color: Red				
SP150GRYPQ		3 Color: Green, Red, Yellow	PNP			
SP150GRYNQ			NPN			
SP150GA120		1 Color: Green	85 to 130V ac		Field-wired	
SP150RA120		1 Color: Red				
SP250GRPQ	2	Top indicator: Red Bottom indicator: Green	PNP	Flat mount polycarbonate	4-pin Euro Integral QD	
SP250GRNQ			NPN		Field-wired	
SP250GRA120			85 to 130V ac			
SP350GYRPQ	3	Top indicator: Red Middle indicator: Yellow Bottom indicator: Green	PNP		4-pin Euro Integral QD	
SP350GYRNQ			NPN			Field-wired
SP350GYRA120			85 to 130V ac			

* For DC models, standard 4-pin Euro integral QD models are listed. AC models are field-wired only.

- For field-wired model, omit suffix **Q** from model number (example, “**SP150GP**”)
- A model with a QD requires a mating cable (see [Quick-Disconnect \(QD\) Cordsets](#) on page 7)

**** 1-color models:** 18 LEDs per color


3-color models: 6 LEDs per color

Contact factory for other colors and color combinations.

Specifications

Feature	Description	
Supply Voltage and Current	DC models: 15 to 30V dc 1-Color: @ 120 mA max. per LED color 3-Color: @ 40 mA max. per LED color	AC models: 85 to 130V ac or 75 to 120V dc @ 16 mA per LED color
Indicators	LED colors are independently selected, depending on model	
Input Response Time	Indicator ON/OFF: 10 ms (max.)	
Environmental Rating (See note 1)	Fully encapsulated; Electronics : IEC IP67 Enclosure : • SP150: IEC IP67 • SP250: IEC IP65 • SP350: IEC IP65	
Connections	Integral 4-pin Euro-style QD or field-wired model available for use with bulk cable (wire nuts included); ½-14 NPSM cord grip is optional for SP150 and SP250 models. Cord grip handles cable diameters from 4.3 to 11.4 mm (see model BWA-CG.5-1).	
Operating Conditions	-40° to +50° C (-40° to +122° F)	
Application Notes	1. Field-wired models must have cover screws tightened and use water tight compression fitting to meet environmental ratings.	

Percent of Maximum Intensity vs Viewing Angle







X: Viewing Angle (Deg)

Y: Intensity (Percent)

PNP Hookups - QD Models

SP150XPQ (1-Color Models)	SP150XXXPQ and SP350XXXPQ (3-Color Models)
SP250XXPQ (2-Color Models)	Wiring Key:
	1 = Brown 2 = White 3 = Blue 4 = Black ⊗ indicates Not Used C1 = Color 1 C2 = Color 2 C3 = Color 3

PNP Hookups - Field-Wired Models

SP150XP (1-Color Models)	SP150XXXP (3-Color Models)	Wiring Key:
		1 = Brown 2 = White 3 = Blue 4 = Black
SP250XP (2-Color Models)	SP350XXXP (3-Color Models)	C1 = Color 1 C2 = Color 2 C3 = Color 3
		




NPN Hookups - QD Models

SP150XPQ (1-Color Models)*	SP150XXXNQ and SP350XXXNQ (3-Color Models)
*NPN functionality using 1-Color PNP model	
SP250XXNQ (2-Color Models)	Wiring Key:
	1 = Brown 2 = White 3 = Blue 4 = Black ⊗ indicates Not Used C1 = Color 1 C2 = Color 2 C3 = Color 3


NPN Hookups - Field-Wired Models

SP150XP (1-Color Models)*	SP150XXXN (3-Color Models)	Wiring Key:
		1 = Brown 2 = White 3 = Blue 4 = Black C1 = Color 1 C2 = Color 2 C3 = Color 3
*NPN functionality using 1-Color PNP model		
SP250XXN (2-Color Models)	SP350XXXN (3-Color Models)	

AC Hookups


SP150XA120 (1-Color Models)	SP350XXXA120 (3-Color Models)
	
SP250XXA120 (2-Color Models)	Wiring Key:
	2 = White 4 = Black C1 = Color 1 C2 = Color 2 C3 = Color 3 N = Neutral

Dimensions - SP150...Models*




* Field-wired models have ½" NPT port in place of M12 connector

Dimensions - SP250...Models*





* Field-wired models have ½" NPT port in place of M12 connector

Dimensions - SP350...Models*



* Field-wired models have access hole for ½" conduit fitting in place of M12 connector
** Mounting kit SMBSP350 included

Quick-Disconnect (QD) Cordsets

4-Pin Euro-Style Cables – Single-Ended				
Style	Model	Length	Dimensions	Pinout
4-pin Euro-style straight	MQDC-406	2 m (6.5')		
	MQDC-415	5 m (15')		
	MQDC-430	9 m (30')		

4-Pin Euro-Style Cables – Single-Ended				
Style	Model	Length	Dimensions	Pinout
4-pin Euro-style Right-angle	MQDC-406RA	2 m (6.5')		1 = Brown 2 = White 3 = Blue 4 = Black
	MQDC-415RA	5 m (15')		
	MQDC-430RA	9 m (30')		

Mounting Brackets

Model		Features	Mounting System	
Stainless Steel	Aluminum	- Elevated-use stand-off pipe (½" NPSM/DN15) - Polished 304 stainless steel or anodized aluminum surface ½ NPT thread at both ends - Compatible with most industrial environments		
SOP-E12-150SS Length: 150 mm (6")	SOP-E12-150A Length: 150 mm (6")			
SOP-E12-300SS Length: 300 mm (12")	SOP-E12-300A Length: 300 mm (12")			
SA-E12M30		- Streamlined acetal mounting base adapter/cover - Connects between ½" NPSM/DN15 pipe and 30 mm (1-3/16") drilled hole - Mounting hardware included		



WARNING . . . Not To Be Used for Personnel Protection

Never use this product as a sensing device for personnel protection. Doing so could lead to serious injury or death

This product does NOT include the self-checking redundant circuitry necessary to allow its use in personnel safety applications. A sensor failure or malfunction can cause either an energized or de-energized sensor output condition. Consult your Banner Safety Products catalog for safety products that meet OSHA, ANSI and IEC standards for personnel protection.