

447-326

Composite Standard Profile EMI/RFI Micro-Banding Backshell

with Self-Locking Rotatable Coupling and Shrink Boot Porch

CONNECTOR DESIGNATOR:

A	MIL-DTL-5015, -26482 Series II, and -83723 Series I and III
F	MIL-DTL-38999 Series I, II
L	MIL-DTL-38999 Series 1.5 (JN1003)
H	MIL-DTL-38999 Series III and IV
G	MIL-DTL-28840
U	DG123 and DG123A

SELF-LOCKING

ROTATABLE COUPLING

STANDARD PROFILE

Product Series

447 - EMI/RFI Non-Environmental Banding Backshells

Angle and Profile

S - Straight
W - 90° Elbow
T - 45° Elbow

Finish Symbol

(See Table III)

Basic Part Number

Cable Entry

(See Table IV)

Drain Hole Option

(Omit "D" if not required)

Shrink Boot Option

Shrink boot and o-ring supplied with **T** option (Omit for none)

447

H

S

326

XM

19

12

D

K

T

S

Connector Designator

A, F, L, H, G and U

Connector Shell Size

(See Table II)

Band Option

B = 600-057
K = 600-057-1
 Bands are Precoiled
 (Omit for none)

Slot Option

S - Pigtail Termin. Slot
 (Omit for none)





TABLE II: CONNECTOR SHELL SIZE

Shell Size For Connector Designator*					E		F		G		Max Entry Dash No.**
A	F/L	H	G	U	± .06	(1.5)	± .09	(2.3)	± .09	(2.3)	
08	08	09	—	—	.69	(17.5)	.88	(22.4)	1.06	(26.9)	04
10	10	11	—	08	.75	(19.1)	1.00	(25.4)	1.13	(28.7)	06
12	12	13	11	10	.81	(20.6)	1.13	(28.7)	1.19	(30.2)	08
14	14	15	13	12	.88	(22.4)	1.31	(33.3)	1.25	(31.8)	10
16	16	17	15	14	.94	(23.9)	1.38	(35.1)	1.31	(33.3)	12
18	18	19	17	16	.97	(24.6)	1.44	(36.6)	1.38	(35.0)	13
20	20	21	19	18	1.06	(26.9)	1.63	(41.4)	1.48	(36.8)	15
22	22	23	—	20	1.13	(28.7)	1.75	(44.5)	1.54	(39.1)	17
24	24	25	23	22	1.19	(30.2)	1.88	(47.8)	1.60	(40.6)	19
28	—	—	25	24	1.34	(34.0)	2.13	(54.1)	1.70	(43.2)	22

**Consult factory for additional entry sizes available.
 See introduction for additional connector front-end details.

TABLE III: FINISH

Symbol	Finish Description
XM	2000 Hour Corrosion Resistant Electroless Nickel
XMT	2000 Hour Corrosion Resistant Ni-PTFE, Nickel-Fluorocarbon Polymer. 1000 Hour Grey™
XW	2000 Hour Corrosion Resistant Cadmium/Olive Drab over Electroless Nickel

447-326
Composite Standard Profile EMI/RFI
Micro-Banding Backshell
with Self-Locking Rotatable Coupling and Shrink Boot Porch




TABLE II: CONNECTOR SHELL SIZE (CONT.)

Shell Size For Connector Designator*					E		F		Max Entry Dash No. (Table 2)
A	F/L	H	G	U	± .06	(1.5)	± .09	(2.3)	
08	08	09	—	—	.72	(18.3)	.87	(22.1)	04
10	10	11	—	08	.75	(19.1)	.93	(23.6)	06
12	12	13	11	10	.75	(19.1)	1.00	(25.4)	08
14	14	15	13	12	.76	(19.3)	1.03	(26.2)	10
16	16	17	15	14	.78	(19.8)	1.05	(26.7)	12
18	18	19	17	16	.79	(20.1)	1.06	(26.9)	13
20	20	21	19	18	.82	(20.8)	1.09	(27.7)	15
22	22	23	—	20	.86	(21.8)	1.13	(28.7)	17
24	24	25	23	22	.89	(22.6)	1.16	(29.5)	19
28	—	—	25	24	.92	(23.4)	1.19	(30.2)	22

TABLE IV: CABLE ENTRY

Entry Code	Entry Dia. ±.03 (0.8)	Dash No.	Entry Dia. ±.03 (0.8)
02	.13 (3.3)	12	.75 (19.1)
03	.19 (4.8)	13	.81 (20.6)
04	.25 (6.4)	14	.88 (22.4)
05	.31 (7.9)	15	.94 (23.9)
06	.38 (9.7)	16	1.00 (25.4)
07	.44 (11.2)	17	1.06 (26.9)
08	.50 (12.7)	18	1.13 (28.7)
09	.56 (14.2)	19	1.19 (30.2)
10	.63 (16.0)	20	1.25 (31.8)
11	.69 (17.5)	22	1.38 (35.1)

NOTES

- 770-001S**-0 shrink boot supplied with T option. See shrink boot product page for more details.
- O-Ring will not be supplied with Connector Designator A.
- Metric dimensions (mm) are in parenthesis and are for reference only.
- Coupling nut supplied unplated.
- See Table I in Intro for front-end dimensional details.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[447AS105NF2007](#) [447FJ164M1208-04B](#) [447HJ747NF1706](#) [447HJ747NF2509](#) [447HS060-19](#) [447HS060-23](#)
[447HS105NF1906](#) [447HS105NF2506](#) [447HS109NF1307-6L](#) [447HS323NF17](#) [447HS326XM0903D](#)
[447HS326XM1103D](#) [447HS326XM1304D](#) [447HS326XM1504](#) [447HS326XM1504D](#) [447HS326XM1505D](#)
[447HS326XM1704D](#) [447HW326XM1103D](#) [447HW326XM1304D](#) [447HZ747NF1907](#) [447HZ747NF2309](#)
[447DS478XW0804](#) [447HS105NF1504](#) [447HS323NF23](#) [447AS317XM10](#) [447HS109NF2506-20L](#) [447HS326XM1103](#)
[447HS326XM1908D](#) [447HS326XM1105D](#) [447HW326XM2512B](#) [447HS326XM1103B](#) [447HW326XM1104B](#)
[447HS531NF2506C](#) [447AS018XX1404R](#) [447HH233NF2316-P](#) [447AS105NF1402](#) [447HS105NF2104](#)
[447HS109NF2116-6L](#) [447HL105NF2105](#) [447AG124M20405](#) [447HJ233NF1911-P](#) [447HS059M21](#) [447HJ310MS2514](#)
[447HF684NF1108](#) [447HJ109NF1509-LPB](#) [447HS646XM2506B](#) [447HS531NF1704C](#) [447HS133NF1502](#)
[447HJ531NF1303](#) [447HH233NF1909-P](#) [447AJ615NF2415](#) [447HS531M1704C](#) [447CS615NF2009N](#)
[447FS615NF1610](#) [447AS771-20](#) [447HD562M23](#) [447FS233NF2206-6P](#) [447SS488N1024](#) [447HS627M1305](#)
[447HS531M1306B](#) [447FW809XW08](#) [447HS449-1508-6B](#) [447HS109NF1912-5LPB](#) [447HS172ZM1513](#)
[447HS109M1106-5](#) [447AS615NF3226](#) [447AJ531NF1203](#) [447HT814XW2115](#) [447HS318Z12518-5](#) [447AS249M1408-](#)
[03](#) [447HS797M2520-3B](#) [447FS022M20](#) [447HS233NF2106-6P](#) [447GS615NF1915](#) [447HS684NF1716-3](#)
[447AJ531NF1605](#) [447AG124M22365](#) [447JS183NF1407](#) [447DS615NF2011](#) [447HS233NF1509-6P](#)
[447NS300NF1508-03](#) [447FD390NF1004](#) [447HS449-0906-6B](#) [447HA557-11A](#) [447HS531NF1107C](#)
[447HL105NF1503K](#) [447HS323NF11](#) [447HJ109B1105-EB-214](#) [447FG088NF20106](#) [447AS105NF2004](#)
[447HS233NF0904-6P](#) [447HJ531NF2105](#) [447HS248XM1306](#) [447HS138NF1112-3](#) [447AS198NF1606-4B](#)
[447LS022NF20](#) [447NS135NF1006-5B](#) [447AS107NF1608-6](#) [447HJ233NF1909-P](#) [447HS198M1712-4B](#)