

High-performance, thin-wall, flexible, fluoropolymer heat-shrinkable tubing

RNF-150 is a highly flame-resistant thin-wall heat-shrinkable tubing that has excellent durability.

It is manufactured from a modified fluoropolymer whose properties include toughness, chemical resistance, and high-temperature performance.

A very thin wall gives RNF-150 excellent flexibility.

Applications include insulation, jacketing, and identification of wire bundles; light-duty harnesses; insulation and protection of terminals and wire connections; and packaging

of components. RNF-150 is not recommended for use in direct contact with ketones.

RNF-150 is UL-recognized at 150°C, 600 V, with a UL VW-1 flame retardance rating and meets the requirements of AMS-DTL-23053/18, Class 2.

Temperature rating

Full recovery temperature:	150°C
Continuous operating temperature:	-55°C to 155°C
Recommended maximum temperature for use as a primary insulator:	135°C


Specifications*



Type	Raychem	Military	UL
RNF-150	RT-370	AMS-DTL-23053/18, Class 2	E85381 VW-1

*When ordering, always specify latest issue.

Dimensions (millimeters/inches)



Size	Inside diameter		Wall thickness			Weight as supplied (max.)	
	D (min.)	d (max.)	W	Recovered after heating**		lb./100 ft.	kg./100 m
	Expanded as supplied	Recovered after heating					
3/64	1.2 0.046	0.6 0.023	0.25 ± 0.05	0.010 ± 0.002		0.10	0.15
1/16	1.6 0.063	0.8 0.031	0.25 ± 0.05	0.010 ± 0.002		0.13	0.19
3/32	2.4 0.093	1.2 0.046	0.25 ± 0.05	0.010 ± 0.002		0.17	0.25
1/8	3.2 0.125	1.6 0.062	0.25 ± 0.05	0.010 ± 0.002		0.22	0.33
3/16	4.8 0.187	2.4 0.093	0.25 ± 0.05	0.010 ± 0.002		0.31	0.46
1/4	6.4 0.250	3.2 0.125	0.30 ± 0.08	0.012 ± 0.003		0.40	0.60
3/8	9.5 0.375	4.8 0.187	0.30 ± 0.08	0.012 ± 0.003		0.73	1.09
1/2	12.7 0.500	6.4 0.250	0.30 ± 0.08	0.012 ± 0.003		0.96	1.43
3/4	19.1 0.750	9.5 0.375	0.43 ± 0.08	0.017 ± 0.003		1.92	2.85
1	25.4 1.000	12.7 0.500	0.48 ± 0.08	0.019 ± 0.003		2.78	4.14

**Wall thickness will be less if tubing recovery is restricted during shrinkage.

Ordering information

Colors	Standard	Black
	Nonstandard	White
Size selection	Always order the largest size that will shrink snugly over the component being covered. Special order sizes may be made available upon request.	
Standard packaging	On spools	
Ordering description	Specify product name, size, and color; for example, RNF-150 1/4-0 (0=Black).	

Specification values

Property	Unit	Requirement	Method of test
Physical	Dimensions	mm (inches)	ASTM D 2671
	Longitudinal change	percent	+0, -10 ASTM D 2671
	Concentricity as supplied	percent	70% minimum ASTM D 2671
	Weight per length as supplied	lb./100 ft. (kg./100 m) max.	See reverse See note below
	Recovery angle	degrees	5 maximum See note below
	Tensile strength	psi (Mpa)	4000 (27.6) minimum ASTM D 2671
	Ultimate elongation	percent	300 minimum ASTM D 2671
	Secant modulus (as supplied)	psi (Mpa)	25,000 to 100,000 (172 to 690) ASTM D 2671
	Low-temperature flexibility (4 hours at -55°C/-67°F)		No cracking AMS-DTL-23053
	Heat shock (4 hours at 250°C/482°F)		No dripping, flowing, or cracking ASTM D 2671
	Dynamic cut-through (135°C/275°F)	lb. (kg.)	5 (2.3) minimum ASTM D 3032 See note below
	Heat resistance (336 hours at 225°C/437°F)		ASTM D 2671
	Followed by test for:		
	Ultimate Elongation	percent	250 minimum ASTM D 2671
Electrical	Color		MIL-STD-104, Class I MIL-STD-104
	Dielectric strength	volts/mil (kV/mm)	500 (19.7) minimum ASTM D 2671
Chemical	Volume resistivity	ohm-cm	10 ¹¹ minimum ASTM D 2671
	Corrosive effect		Noncorrosive ASTM D 2671
	Copper mirror corrosion (16 hours at 160°C/320°F)		Copper removal 5% maximum ASTM D 2671 Procedure A
	Copper contact corrosion (16 hours at 175°C/347°F)		No blackening or pitting of copper ASTM D 2671 Procedure B
	Copper stability (168 hours at 180°C/356°F)		No brittleness, glazing, or severe discoloration of tubing. No pitting or blackening of copper. ASTM D 2671 Procedure B
	Followed by test for:		
	Ultimate elongation	percent	250 minimum ASTM D 2671
	Flammability		25% maximum flag burn; no burning of cotton; no flaming or glowing longer than 60 seconds UL 224, VW-1 ASTM D 2671 Procedure C
	Fungus resistance		ISO 846 Method B
	Followed by tests for:		
	Tensile strength	psi (Mpa)	4000 (27.6) minimum ASTM D 2671
	Ultimate elongation	percent	300 minimum ASTM D 2671
	Dielectric strength	volts/mil (kV/mm)	500 (19.7) minimum ASTM D 2671
	Water absorption (24 hours at 23°C/73°F)	percent	0.5 maximum ASTM D 2671
	Fluid resistance (24 hours at 50°C/122°F) in:		ASTM D 2671
	JP-8 fuel (MIL-T-5624)		
	Hydraulic fluid (MIL-H-5606)		
	Aviation gasoline 100/300 (MIL-G-5572)		
	Water		
	Lubricating oil (MIL-L-23699)		
	Followed by tests for:		
	Dielectric strength	volts/mil (kV/mm)	400 (15.8) minimum ASTM D 2671
	Tensile strength	psi (Mpa)	2000 (13.8) minimum ASTM D 2671

Note: Consult RT-370 for specific details about test procedures.

Raychem is a trademark of Tyco Electronics Corporation.

Users should independently evaluate the suitability of the product for their application.

Tyco Electronics Corporation

300 Constitution Drive
Menlo Park, CA 94025-1164
USA
Tel: (800) 926-2425 (US & Canada)
Tel: +1 (650) 361-3860 (All other countries)

Faraday Road
Dorcan, Swindon, SN3 5HH
United Kingdom
Tel: +44 1793 528171

3816 Noborito, Tama-ku
Kawasaki, Kanagawa 214-8533
Japan
Tel: +81 44 900 5102

Asia Pacific Headquarters
26 Ang Mo Kio, Industrial Park 2
Singapore 569507
Tel: +65 4866 151

All information, including illustrations, is believed to be reliable. Users, however, should independently evaluate the suitability of each product for their application. Tyco Electronics Corporation makes no warranties as to the accuracy or completeness of the information, and disclaims any liability regarding its use. Tyco Electronics Corporation's only obligations are those in the Standard Terms and Conditions of Sale for these products and in no case will Tyco Electronics Corporation be liable for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of the product. Tyco Electronics Corporation's Specifications are subject to change without notice. In addition, Tyco Electronics Corporation reserves the right to make changes in materials or processing without notification to the Buyer which do not affect compliance with any applicable specification.

For more information about this product visit www.tycoelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RNF-150-1/4-0-SP](#) [RNF-150-1/16-0-SP](#) [RNF-150-1/2-0-SP](#) [RNF-150-1/8-0-SP](#) [RNF-150-1-0-SP](#) [RNF-150-3/16-0-SP](#) [RNF-150-3/32-0-SP](#) [RNF-150-3/4-0-SP](#) [RNF-150-3/64-0-SP](#) [RNF-150-3/8-0-SP](#) [RNF-150-1/8-9-SP](#)