

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

41662-0007

Status:


Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 396 Breakaway Header, Right-Angle, 8 Circuits, 0.38µm Gold (Au) Selective Plating



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-08-50 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

41662

Application

Board-to-Board, Power, Wire-to-Board

Application Tooling Part Link

11-20-0901

Overview

KK® Interconnect System - Molex

Product Name

KK® 396

UPC

756054447864

Physical

Breakaway

Yes

Circuits (Loaded)

8

Circuits (maximum)

8

Color - Resin

Black

Durability (mating cycles max)

50

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

Polyester

Net Weight

2.915/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

4.67mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

3.96mm

Pitch - Termination Interface

3.96mm

Plating min - Mating

0.381µm

Plating min - Termination

2.540µm

Polarized to Mating Part

Yes

Polarized to PCB

No

Shrouded

Partial

Stackable

No

Temperature Range - Operating

See Product Specification

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

41662Series

Mates With

2139 KK® Crimp Housing, 41695 KK®
Crimp Housing, 6442 KK® Crimp Housing,
2145 PCB Connector, 41815 PCB
Connector, 3069 KK® Crimp Housing

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	7A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235
Material Info	
Old Part Number	A-41662-B08Y208
Reference - Drawing Numbers	
Product Specification	PS-08-50
Sales Drawing	SD-41662-001

This document was generated on 07/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[41662-0007](#)