



KZ

Premium Grade Type, For Audio Equipment


series



For Audio Use Anti-Solvent Feature

- Premium grade "nichicon MUSE" acoustic series.
- Ideally suited for first class audio equipment where qualitative and quantitative comfortableness is required.
- Compliant to the RoHS directive (2002/95/EC).


KZ High Grade FG




Specifications

Item	Performance Characteristics				
Category Temperature Range	-40 to +85°C				
Rated Voltage Range	25 to 100V				
Rated Capacitance Range	10 to 1000μF				
Capacitance Tolerance	±20% at 120Hz, 20°C				
Leakage Current	After 1 minute's application of rated voltage, leakage current is 0.01CV or less.				
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz, Temperature : 20°C				
	Rated voltage (V)	25	50	100	
	tan δ (MAX.)	0.12	0.08	0.07	
Stability at Low Temperature	Measurement frequency : 120Hz				
	Rated voltage (V)		25	50	100
	Impedance ratio ZT / Z20 (MAX.)	Z-25°C / Z+20°C	2	2	2
		Z-40°C / Z+20°C	4	3	3
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 85°C.		Capacitance change	Within ±20% of the initial capacitance value	
			tan δ	150% or less than the initial specified value	
			Leakage Current	Less than or equal to the initial specified value	
Shelf Life	After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.				
Marking	Printed with gold color letter on black sleeve.				

Radial Lead Type



Type numbering system (Example : 25V 100μF)



• Please refer to page 20 about the end seal configuration.

Dimensions

		φD×L (mm)			
Cap.(μF)	V	25	50	100	
	Code	1E	1H	2A	
10	100				8×11.5
22	220		8×11.5		10×16
33	330	8×11.5	10×12.5		10×20
47	470	10×12.5	10×16		12.5×20
100	101	10×16	12.5×20		16×25
220	221	12.5×20	16×25		16×35.5
330	331	12.5×25	16×31.5		18×35.5
470	471	16×25	16×35.5		
1000	102	16×35.5	18×40		

Please refer to page 20, 21, 22 about the formed or taped product spec.
Please refer to page 4 for the minimum order quantity.