





NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
- 3 - CIRCUIT DIAGRAM AND CATALOG LISTING,
CUSTOMER PART NO. AND DATE CODE
ARE SHOWN ON NAMEPLATE
- 4 - COINCIDENCE OF OPERATING AND RELEASING
POINTS: .010 OF PLUNGER TRAVEL
- 5 - HARDWARE MAY BE PACKAGED UNASSEMBLED
PER MIL-PRF-8805
- 6 - THIS DESIGN IS FOR INLINE ACTUATION
- 7 - HEAT SHRINK TUBING IS POTTED INSIDE HOUSING

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH			THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE ----- 4-8 LBS FULL OVERTRAVEL FORCE -----20 LBS MAX RELEASE FORCE ----- 3 LBS MIN PRETRAVEL .----- .015-.040 DIFFERENTIAL TRAVEL----- .020 MAX TOTAL TRAVEL ----- .900 MIN		CONTACT ARRANGEMENT 2X S P D T		DO NOT SCALE PRINT
		LOAD 28 VDC		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
		SEA LEVEL	50,000 FT	ONE PLACE (.0) ±.030
RES		4	4	TWO PLACE (.00) ±.015
IND		2	2	THREE PLACE (.000) ±.005
MOTOR				ANGLES ±
				WEIGHT 6 OZ MAX

ANSI Y14.5M-1982 APPLIES