

# W-Series Switch

Carling Technologies set the standard for performance and aesthetics with the widely successful, often imitated but never duplicated, V-Series rocker switches. Building further upon that platform, Carling has once again raised the bar with the fully sealed W-Series. The W-Series' traditional appearance features complete IP68 protection, including below the panel, where the critical connection is made from wiring harness. When used in conjunction with the integrated connector, the totally submersible W-Series provides a seal for up to ten individual wires, assuring compatibility with even the most complex circuitry.

The W-Series also offers a wide variety of accoutrements including endless illumination options featuring dual level and multicolor LEDs, progressive and hazard warning circuits, ratings up to 10A 24V, choice of paddle, rocker, locking or laser etched actuators, hundreds of standard legend choices and the electrical performance and reliability that is the hallmark of Carling Technologies products.



#### Key Features:

- ♦ Fully sealed and submersible
- ♦ IP68 protection including below the panel
- ♦ Tri-seal design
- ♦ Connector with twin locking tabs

#### Typical Applications:

- ♦ Marine equipment
- ♦ Transportation equipment



**Carling Technologies®**

Innovative Designs. Powerful Solutions.

Innovative Designs. Powerful Solutions.

Carling Technologies, Inc.  
60 Johnson Avenue • Plainville, CT 06062-1177  
Phone: (860) 793-9281 • Fax: (860) 793-9231  
Email: [sales@carlingtech.com](mailto:sales@carlingtech.com) • [www.carlingtech.com](http://www.carlingtech.com)

# W-Series Switch


## DESIGN FEATURES

### TRI-SEAL DESIGN

Affords IP68 protection for the entire switch including terminals and connector.

### CONNECTOR WITH TWIN LOCKING TABS

Provides sealed water tight connections as simple removal using only your hands.



### AN EASY RETROFIT

Fits industry standard mounting hole 1.450 x .830 [36.83mm x 21.08mm].

### FUNCTIONALITY UNDER EXTREME CONDITIONS

Roller pin mechanism is lubricant free, withstanding temperatures from -40°C to +85°C.

### PROVEN SWITCH MECHANISM

Butt-Action contacts are available in a wide variety of circuitry and platings to accommodate most any application.

## Electrical

|                            |                                                                    |
|----------------------------|--------------------------------------------------------------------|
| Contact Rating             | .4VA @ 24VDC<br>10 amps, 3-24VDC                                   |
| Dielectric Strength        | 1500 Volts RMS                                                     |
| Insulation Resistance      | 50 Megaohms                                                        |
| Initial Contact Resistance | 10 milliohms max. @ 4 VDC                                          |
| Life                       | 100,000 cycles                                                     |
| Contacts                   | Silver tin-oxide, 88/12                                            |
| Terminals                  | Copper with silver or gold plating.<br>Quick Connect terminations. |
| Voltage                    | 3-24 VDC                                                           |
| Overcurrent                | 15A for 50 cycles                                                  |

## Mechanical

|           |                        |
|-----------|------------------------|
| Endurance | 250,000 cycles minimum |
|-----------|------------------------|

## Physical

|           |                                                                                                                    |
|-----------|--------------------------------------------------------------------------------------------------------------------|
| Lighted   | LED - rated 100,000 hours 1/2 life<br>(LED is internally ballasted for voltages to 24 VDC)                         |
| Seals     | Neoprene                                                                                                           |
| Base      | Polyester blend rated to 125C with a UL flammability rating of 94V0.                                               |
| Actuator  | Basic actuator structure molded of thermoplastic polycarbonate with a hard Nylon 66 thermoplastic surface overlay. |
| Lens      | Polycarbonate rated at 100°C                                                                                       |
| Function  | 2 & 3 Position Rocker Style                                                                                        |
| Operation | Maintained & Momentary                                                                                             |
| Base      | PA 6/6 30GF (glass filled)                                                                                         |
| Actuator  | PA 6/6 13GF                                                                                                        |
| Bracket   | PBT 10GF                                                                                                           |
| Connector | PBT 10GF, polarized                                                                                                |

## Actuator Travel (Angular Displacement)

24° full throw


## Environmental

|                                  |                                                                                                                                                                                                       |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environmental                    | IP68, Fully sealed                                                                                                                                                                                    |
| Corrosion/<br>Chemical Splash    | Flowing Mixed Gas (FMG)<br>Class III 3 year accelerated exposure per ASTM B-827, B-845                                                                                                                |
| Operating Temperature            | -40°C to +85°C, 22 cycles, 300 hours                                                                                                                                                                  |
| Vibration 1                      | Per Mil-Std 202F, Method 204D Test Condition A 0.06 DA or 10G's 10-500 Hz.                                                                                                                            |
| Vibration 2                      | Resonance search<br>24-50 Hz 0.40 DA<br>50-2000 ±10 G's peak<br>Results Horizontal Axis 3-5 G's max.<br>Random<br>24 Hz 0.06 PSD-Gsq/Hz<br>60 Hz 0.50<br>100 Hz 0.50<br>200 Hz 0.025<br>2000 Hz 0.025 |
| Handling/Drop                    | One meter onto concrete floor                                                                                                                                                                         |
| Salt Spray                       | Per Mil-Std 202F, Method 101D, Test Condition A, 48 Hrs.                                                                                                                                              |
| Dust                             | IP6X                                                                                                                                                                                                  |
| Thermal Shock                    | Per Mil-Std 202F, Method 107F, Test Condition A, -55°C to 85°C. Test criteria - pre and post test contact resistance                                                                                  |
| Moisture Resistance/<br>Humidity | Per Mil-Std 202F, Method 106F, Test Criteria - pre and post test contact resistance                                                                                                                   |




## Mounting Specifications

Panel Thickness Range .032 to .125


For optimum panel fit, the following panel thicknesses are suggested: .032, .062, .093, .125



## Dimensional Specifications: in. [mm]



WCH CONNECTOR  
(190-31214-001)



### Notes:

WCH connector is intended for use with Tyco/Amp .110 Junior Power Timer, female contacts, and wire seals.  
For 14-16 awg wire, specify Tyco/Amp P/N 927766-3  
For 16-20 awg wire, specify Tyco/Amp P/N 927770-3  
Tyco/Amp cable seal P/N 828904-1 (20-18 awg wire) or P/N 828905-1 (16-14 awg wire) is required for each individual wire lead, and Tyco/Amp cable plug, P/N 828922-1, is required to seal each unused connector opening. Consult Tyco/Amp for the cable seal recommended for your specific wire gauge and thickness.

|             |              |             |                  |                   |           |           |              |   |               |            |            |              |   |                             |                               |
|-------------|--------------|-------------|------------------|-------------------|-----------|-----------|--------------|---|---------------|------------|------------|--------------|---|-----------------------------|-------------------------------|
| W           | 11           | D           | 2                | B                 | C         | 0         | 1            | — | A             | 7          | Z          | 00           | — | 0                           | 00                            |
| 1<br>Series | 2<br>Circuit | 3<br>Rating | 4<br>Termination | 5<br>Illumination | 6<br>Lamp | 7<br>Lamp | 8<br>Bracket |   | 9<br>Actuator | 10<br>Lens | 11<br>Lens | 12<br>Legend |   | 13<br>Legend<br>Orientation | 14<br>Actuator<br>Lens Legend |

### 1 SERIES W

### 2 CIRCUIT

Terminal Connections as viewed from bottom of switch:

|            |             |
|------------|-------------|
| 8 terminal | 10 terminal |
| 8 - 7      | 8 - 7       |
| 1 - 4      | 1 - 4       |
| 2 - 5      | 2 - 5       |
| 3 - 6      | 3 - 6       |
|            | 10 - 9      |

( ) - momentary

SP - single pole - uses terminals 1, 2 & 3.  
DP - double pole uses terminals 1, 2, 3, 4, 5 & 6.  
Terminals 7, 8, 9 & 10 for lamp circuit only.

### Position:

| SP | DP | 1            | 2                   | 3            |
|----|----|--------------|---------------------|--------------|
| 21 | 21 | 2 & 3, 6 & 8 | Connected Terminals | 1 & 2, 5 & 6 |
| 12 | 22 | ON           | NONE                | OFF          |
| 13 | 23 | ON           | NONE                | OFF          |
| 14 | 24 | ON           | NONE                | ON           |
| 15 | 25 | ON           | NONE                | ON           |
| 16 | 26 | ON           | OFF                 | ON           |
| 17 | 27 | ON           | OFF                 | ON           |
| 18 | 28 | ON           | OFF                 | ON           |
| -  | 49 | ON           | ON                  | ON           |

### 3 RATING

|   |         |
|---|---------|
| B | 10A 24V |
| D | 10A 12V |
| G | 10A 6V  |
| H | 10A 3V  |

### 4 TERMINATION/BASE STYLE

2 .110 TAB (QC)

### 5 ILLUMINATION

Lamp #1: above terminals 1 & 4 end of switch.; Lamp #2: above terminals 3 & 6 end of switch.  
Positive (+) and negative (-) symbols apply to LED lamps only

|   | Lamps   | Actuator Lens Position<br>Illumination Type | Lamp wired to Terminals |
|---|---------|---------------------------------------------|-------------------------|
| O | NONE    |                                             |                         |
| A | # 1     | Independent                                 | 8+ 7-                   |
| B | # 1     | Down                                        | 3+ 7-                   |
| C | # 2     | Up                                          | 3+ 7-                   |
| D | # 1     | Down                                        | 3+ 7-                   |
| E | & # 2   | Down                                        | 1+ 7-                   |
| F | # 1     | Up                                          | 1+ 7-                   |
| G | & # 2   | Up                                          | 3+ 7-                   |
| H | # 1     | Independent                                 | 8+ 7-                   |
| I | & # 2   | Up                                          | 3+ 7-                   |
| J | # 2     | Independent                                 | 8+ 7-                   |
| K | # 1     | Down                                        | 3+ 8-                   |
| L | & # 2   | Independent                                 | 6+ 7-                   |
| M | # 1     | Independent                                 | 8+ 7-                   |
| N | # 2     | Independent                                 | 6+ 7-                   |
| P | # 1     | Independent                                 | 8+ 7-                   |
| Q | & # 2   | Independent                                 | 6+ 7-                   |
| R | # 1     | Independent                                 | 8+ 7-                   |
| S | & # 2   | Independent                                 | 6+ 7-                   |
| T | # 1     | Independent                                 | 8+ 7-                   |
| U | & # 2   | Independent                                 | 8+ 7-                   |
| V | # 1     | Independent                                 | 10+ 9-                  |
| W | & # 2   | Independent                                 | 10+ 9-                  |
| X | # 1     | Independent                                 | 8+ 7-                   |
| Y | & # 2   | Independent                                 | 10+ 7-                  |
| Z | # 1 & 2 | Independent in Series                       | 8+ 7-                   |
|   | # 1 & 2 | Independent in Parallel                     | 8+ 7-                   |

### 6,7 LAMP (SAME CODING FOR BOTH SELECTIONS)

Selection 6: above terminals 1 & 4; Selection 7: above terminals 3 & 6

No lamp 0

LED\*

|       | Red | Amber | superbright<br>Green | White |
|-------|-----|-------|----------------------|-------|
| 2VDC  | A   | L     | F                    | 4     |
| 6VDC  | B   | M     | G                    | 5     |
| 12VDC | C   | N     | H                    | 6     |
| 24VDC | D   | P     | J                    | 8     |

\* Consult factory for "daylight bright", blue/green and white LED options.

Typical current draw for LED is 20ma.

### 8 BRACKET COLOR<sup>1</sup>

1 Black

### 9 ACTUATOR<sup>1,3</sup>

3 Black with Laser Etch

A Black

### 10 LENS - ABOVE LAMP #1 TERMINALS<sup>1,4</sup>

### 11 LENS - ABOVE LAMP #2 TERMINALS<sup>3,6</sup>

Lens color for LEDs must be clear, white, or match color of LED.

0 - No Actuator Z - No Lens

| Clear | White | Amber | Green | Red | Blue                        |
|-------|-------|-------|-------|-----|-----------------------------|
| 1 -   | B     | G     | M     | T   | Large Transparent           |
| - 7   | C     | H     | N     | U   | Large Translucent           |
| 3 -   | D     | J     | P     | V   | Bar Transparent             |
| - 9   | E     | K     | R     | W   | Bar Translucent             |
| 5 A   | -     | -     | -     | -   | Laser Etch background color |

### 12 ACTUATOR LENS OR BODY LEGEND<sup>2</sup>

00 - No Legend this location/No actuator

11 ON 12 OFF 13 I 14 O  
OFF ON O I

15 O O 16 O O 17 O I 18 I O  
F N F F F

21 OFF 22 ON 23 O 24 I  
F F N

25 O 26 O 27 O 28 I  
F N

For additional legend options & codes, see pages 54-65 of the Carling Transportation catalog

### 13 LEGEND ORIENTATION

0 No legend (used with codes 11-18 in selection 12)


1 Orientation 1  
2 Orientation 2  
3 Orientation 3  
4 Orientation 4



AY3-200



AY3-100



### 14 ACTUATOR LENS LEGEND<sup>2</sup>

00 No legend this location/no actuator (used with codes 11-18 in selection 12)

Selection 14 required when switch requires two legends. If the two legends consist of one lens & one body legend, lens legend must be specified in selection 12; body legend specified in selection 14. For legend options & codes, see pages 54-65 of the Carling Transportation catalog.

### Notes:

- Custom colors are available. Consult factory.
- White imprinting is standard on black actuators; Black imprinting is standard on white, red & gray actuators; Custom colors are available, consult factory.
- Locking rocker version is also available, consult factory for details.

\* Intentionally left blank

\* Intentionally left blank

### **Worldwide Headquarters**

Carling Technologies, Inc.  
60 Johnson Avenue • Plainville, CT 06062-1177  
Phone: (860) 793-9281 • Fax: (860) 793-9231  
Email: sales@carlingtech.com • www.carlingtech.com

East Region Sales Office, CT • ersm@carlingtech.com  
Midwest Region Sales Office, IL • mrsn@carlingtech.com  
West Region Sales Office, CA • wrsm@carlingtech.com

### **Asia-Pacific Headquarters**

Carling Technologies, Asia-Pacific Ltd.,  
Kowloon, Hong Kong  
Int + 852-2737-2277 • Fax: Int + 852-2736-9332  
Email: sales@carlingtech.com.hk

Shenzhen, China • shenzhen@carlingtech.com  
Shanghai, China • shanghai@carlingtech.com  
Pune, India • india@carlingtech.com  
Kaohsiung, Taiwan • taiwan@carlingtech.com  
Yokohama, Japan • japan@carlingtech.com

### **Europe / Middle East / Africa Headquarters**

Carling Technologies, Ltd.,  
Devon, England 06062-1177  
Int + 44 1392-364422 • Fax: Int + 44 1392-364477  
Email: ltd.sales@carlingtech.com

GmbH, Germany • gmbh@carlingtech.com  
SAS, France • sas@carlingtech.com

REV\_SW\_W\_0412



**Carling Technologies™**

Innovative Designs. Powerful Solutions.

Innovative Designs. Powerful Solutions.