




- Low noise, smooth operation
- In accordance with “Mil” RV4N, RV4L, RV6L, RV6N, 2RV7N types
- RoHS compliant; non-RoHS version unavailable.

Since all rheostats/potentiometers are electro-mechanical devices, they are subject to mechanical wear and, therefore, have a finite life.

Molded composition



Model	Watts	Ohmic range	Behind panel (In./mm)	Diameter (In./mm)	Rotation	Voltage (RMS)
AS	0.5	50-5M	0.703/17.9	0.50/12.7	295° ±5°	350
ASM	0.5	50-5M	0.703/17.9	0.50/12.7	295° ±5°	350
CA	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500
CB	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500
CU	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500
CCU	2.0	50-5M	1.266/32.1	1.16/29.4	312° ±3°	500
CLU	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500
CMU	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500

Ohmic value	MIL Designation						Linear
	Prefix ▶ Suffix ▼		Part No. Prefix ▶ Suffix ▼				
	RV4NAYSJ CVU	RV4NAYSJ CU	RV4NAYSJ CA	RV4NAYSJ CB	RV4LAYSJ CLU	RV6NAYSJ CCU	
50 — 500A — 500I	✓	✓			✓		
100 — 101A — 101I	✓	✓				✓ AS3601E	✓ ASM6661E
150 — 151A — 151I	✓	✓			✓		
250 — 251A — 251I	✓	✓			✓	✓ AS3602E	✓ ASM6662E
350 — 351A — 351I	✓	✓			✓		
500 — 501A — 501I	✓	✓			✓	✓ AS3603E	✓ ASM6663E
750 — 751A — 751I	✓	✓					
1,000 — 102A — 102I	✓	✓			✓	✓ AS3604E	✓ ASM6664E
1,500 — 152A — 152I	✓	✓			✓		
2,500 — 252A — 252I	✓	✓			✓	✓ AS3605E	✓ ASM6665E
3,500 — 352A — 352I	✓	✓			✓		
5,000 — 502A — 502I	✓	✓				✓ AS3606E	✓ ASM6666E
7,500 — 752A — 752I	✓	✓			✓		
10,000 — 103A — 103I	✓	✓		✓	✓	✓ AS3607E	✓ ASM6667E
15,000 — 153A — 153I	✓	✓		✓			
25,000 — 253A — 253I	✓	✓		✓	✓	✓ AS3608E	✓ ASM6668E
35,000 — 353A — 353I	✓	✓		✓			

* add “-E” for RoHS-compliant lead-free zinc-nickel plated product

Check product availability at www.ohmite.com