




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 2	REDRAWN ON CAD ECN 92-0009	8/13/93	 8/13/93

ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ohms) <u>50</u>	Interface Dimensions MIL-STD-348, Fig.310-2	Temperature Rating <u>-65°C To 105°C</u>
Frequency Range (GHz) DC to <u>18</u>	Recommended Mating Torque <u>7-10 In-Lbs</u>	Vibration MIL-STD-202, Method 204, Condition B
Volt Rating (VRMS MAX) ⊗ Sea Level <u>85</u>	Mating Characteristics: Insertion (MAX Lbs) <u>2.0</u>	Shock MIL-STD-202, Method 213, Condition I
VSWR <u>N/A</u>	Withdrawal (MIN Oz) <u>1.0</u>	Thermal Shock MIL-STD-202, Method 107, Condition A,
Insertion Loss (dB MAX) <u>N/A</u>	Force to Engage and Disengage (In/Lbs MAX) <u>2</u>	Moisture Resistance MIL-STD-202, Method 106, Except Vibration Shall Be Omitted
RF Leakage (dB MIN) <u>-60dB</u>	Center Contact Captivation Axial (Lbs) <u>6.0</u>	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray
Corona, 70,000 Ft (VRMS MIN) <u>250</u>	Radial (In/Oz) <u>4.0</u>	
Dielectric Withstanding Voltage (VRMS MIN) ⊗ Sea Level <u>1000</u>	Weight (Grams) _____	
Contact Resistance (Milliohms MAX) Center Contact <u>3.0</u>		
Outer Contact <u>2.0</u>		
Cable to Housing <u>N/A</u>		
RF High Potential ⊗ Sea Level (VRMS MIN ⊗ 5 MHz) <u>670</u>		
I.R.(Megohms MIN) <u>5000</u>		
		<u>.XXX=INCHES</u> <u>X.X=MILLIMETERS</u>

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± °	DRAWN BY RMK CHECKED BY BWC APPROVED BY D. N. ANANIA	DATE 9/19/69 9/22/69 9/24/69
These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE NO. AP. N/A	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599 TITLE OSM FLANGE MOUNT JACK RECEPTACLE - SOLDER POT TERMINAL SIZE B CODE IDENT NO. 26805 2052-1350-00 REV 01 2 SCALE 5:1 SHEET 1 OF 1

AMP PART # 1052543-1
SHEET 1 OF 1 REV A