

100731/730/723/720

JOBBER DRILLS


Straight Shank

Standard Helix

BS 328 DIN 338 ISO 235/1

	Range	Finish
01 000 HSS	1/16"-3/4" 1.55mm-25.00mm	P1 Blue P1 Blue
01 030 HSS	1/64"-3/4" 0.30mm-25.00mm	Bright Bright
01 005 HSS	3/64"-3/4" 1.00mm-20.00mm	TiN TiN

Point Angle 118° General Purpose



Dia in d	Flute Length mm l ₂	Overall Length mm l ₁	01000 01030 Availability	01005
----------------	---	---	--------------------------------	-------

Dia in d	Flute Length mm l ₂	Overall Length mm l ₁	01000 01030 Availability	01005
----------------	---	---	--------------------------------	-------

Dia in d	Flute Length mm l ₂	Overall Length mm l ₁	01000 01030 Availability	01005
----------------	---	---	--------------------------------	-------

*0.30	4	19	•	-
*0.32	4	19	•	-
*0.35	4	19	•	-
*0.38	4	19	•	-
*1/64	5	20	•	-
*0.40	5	20	•	-
*0.42	5	20	•	-
*0.45	5	20	•	-
*0.48	5	20	•	-
*0.50	6	22	•	-
*0.52	6	22	•	-
*0.55	7	24	•	-
*0.58	7	24	•	-
*0.60	7	24	•	-
*0.62	8	26	•	-
*0.65	8	26	•	-
*0.68	9	28	•	-
*0.70	9	28	•	-
*0.72	9	28	•	-
*0.75	9	28	•	-
*0.78	10	30	•	-
*1/32	10	30	•	-
*0.80	10	30	•	-
*0.82	10	30	•	-
*0.85	10	30	•	-
*0.88	11	32	•	-
*0.90	11	32	•	-
*0.92	11	32	•	-
*0.95	11	32	•	-
*0.98	12	34	•	-
*1.00	12	34	•	•
*1.05	12	34	•	•
*1.10	14	36	•	•
*1.15	14	36	•	•
*3/64	16	38	•	•
*1.20	16	38	•	•
*1.25	16	38	•	•
*1.30	16	38	•	•
*1.35	18	40	•	•
*1.40	18	40	•	•
*1.45	18	40	•	•
*1.50	18	40	•	•
1.55	20	43	•	•
1/16	20	43	•	•
1.60	20	43	•	•
1.65	20	43	•	•
1.70	20	43	•	•
1.75	22	46	•	•

1.80	22	46	•	•
1.85	22	46	•	•
1.90	22	46	•	•
1.95	24	49	•	•
5/64	24	49	•	•
2.00	24	49	•	•
2.05	24	49	•	•
2.10	24	49	•	•
2.15	27	53	•	•
2.20	27	53	•	•
2.25	27	53	•	•
2.30	27	53	•	•
2.35	27	53	•	•
3/32	30	57	•	•
2.40	30	57	•	•
2.45	30	57	•	•
2.50	30	57	•	•
2.55	30	57	•	•
2.60	30	57	•	•
2.65	30	57	•	•
2.70	33	61	•	•
2.75	33	61	•	•
7/64	33	61	•	•
2.80	33	61	•	•
2.85	33	61	•	•
2.90	33	61	•	•
2.95	33	61	•	•
3.00	33	61	•	•
3.05	36	65	•	•
3.10	36	65	•	•
3.15	36	65	•	•
1/8	36	65	•	•
3.20	36	65	•	•
3.25	36	65	•	•
3.30	36	65	•	•
3.35	36	65	•	•
3.40	39	70	•	•
3.45	39	70	•	•
3.50	39	70	•	•
3.55	39	70	•	•
9/64	39	70	•	•
3.60	39	70	•	•
3.65	39	70	•	•
3.70	39	70	•	•
3.75	39	70	•	•
3.80	43	75	•	•
3.85	43	75	•	•
3.90	43	75	•	•

5/32	3.95	43	75	•	•
	4.00	43	75	•	•
	4.05	43	75	•	•
	4.10	43	75	•	•
	4.15	43	75	•	•
	4.20	43	75	•	•
	4.25	43	75	•	•
	4.30	47	80	•	•
	4.35	47	80	•	•
11/64	4.40	47	80	•	•
	4.45	47	80	•	•
	4.50	47	80	•	•
	4.55	47	80	•	•
	4.60	47	80	•	•
	4.65	47	80	•	•
	4.70	47	80	•	•
	4.75	47	80	•	•
3/16	4.80	52	86	•	•
	4.85	52	86	•	•
	4.90	52	86	•	•
	4.95	52	86	•	•
	5.00	52	86	•	•
	5.10	52	86	•	•
	5.15	52	86	•	•
13/64	5.20	52	86	•	•
	5.25	52	86	•	•
	5.30	52	86	•	•
	5.35	57	93	•	•
	5.40	57	93	•	•
	5.45	57	93	•	•
	5.50	57	93	•	•
7/32	5.60	57	93	•	•
	5.65	57	93	•	•
	5.70	57	93	•	•
	5.75	57	93	•	•
	5.80	57	93	•	•
	5.85	57	93	•	•
	5.90	57	93	•	•
15/64	6.00	57	93	•	•
	6.05	63	101	•	•
	6.10	63	101	•	•
	6.15	63	101	•	•

Standard Helix

Range

Finish

1/16"-3/4"

1.55mm-25.00mm

P1 Blue

P1 Blue

1/64"-3/4"

0.30mm-25.00mm

Bright

Bright
Bright


3/64"-3/4"

1.00mm-20.00mm

TiN

TiN
TiN

Point Angle 118° General Purpose

13

Continued on page 14


J O B B E R D R I L L S

Straight Shank

Standard Helix

BS 328 DIN 338 ISO 235/1

	Range	Finish
01 000 HSS	1/16"-3/4" 1.55mm-25.00mm	P1 Blue P1 Blue
01 030 HSS	1/64"-3/4" 0.30mm-25.00mm	Bright Bright
01 005 HSS	3/64"-3/4" 1.00mm-20.00mm	TiN TiN



Point Angle 118° General Purpose

Dia in d	Flute Length mm l ₂	Overall Length mm l ₁	01000 01030 Availability	01005
----------------	---	---	--------------------------------	-------

	13.20	101	151	•	•
	13.25	108	160	•	•
	13.30	108	160	•	•
	13.40	108	160	•	•
17/32		108	160	•	•
	13.50	108	160	•	•
	13.60	108	160	•	•
	13.70	108	160	•	•
	13.75	108	160	•	•
	13.80	108	160	•	•
35/64		108	160	•	•
	13.90	108	160	•	•
	14.00	108	160	•	•
	14.25	114	169	•	•
9/16		114	169	•	•
	14.50	114	169	•	•
37/64		114	169	•	•
	14.75	114	169	•	•
	15.00	114	169	•	•
19/32		120	178	•	•
	15.25	120	178	•	•
39/64		120	178	•	•
	15.50	120	178	•	•
	15.75	120	178	•	•
5/8		120	178	•	•
	16.00	120	178	•	•
41/64		125	184	•	•
	16.50	125	184	•	•
21/32		125	184	•	•
	17.00	125	184	•	•
43/64		130	191	•	•
11/16		130	191	•	•
	17.50	130	191	•	•
	18.00	130	191	•	•
23/32		135	198	•	•
	18.50	135	198	•	•
	19.00	135	198	•	•
3/4		140	205	•	•
	19.50	140	205	•	•
25/32		140	205	•	•
	20.00	140	205	•	•
	21.00	145	213	•	-
	22.00	150	221	•	-
	23.00	155	229	•	-
	24.00	160	236	•	-
	25.00	160	236		