


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1296	C	Updated Parts List	HO	12/11/01	JC	12/11/01	JC	12/11/01
1576	D	Remove P/N DSC-100B	HO	8/14/03	JC	8/14/03	JC	8/14/03



SPC Type No.	Dimensions			Material	Color
	Length	Height	width		
DSC-100A	1.98	1.21	.065	CRYSTAL POLYSTYRENE	CLEAR
3572	1.05	1.32	.06	CLEAR POLYPROPYLENE	CLEAR/TRANSLUCENT
3573	1.34	1.17	.06	CLEAR POLYPROPYLENE	CLEAR/TRANSLUCENT
3574	1.68	1.55	.06	CLEAR POLYPROPYLENE	CLEAR/TRANSLUCENT
3575	2	1.78	.06	CLEAR POLYPROPYLENE	CLEAR/TRANSLUCENT
3576	1.07	1.26	.106	POLYETHYLENE	TRANSLUCENT
3577	1.68	1.58	.109	POLYETHYLENE	TRANSLUCENT
1710	2.08	1.91	.128	POLYETHYLENE	TRANSLUCENT
DC300-1	1.98	1.20	.066	CONDUCTIVE POLYPROPYLENE	BLACK
DC300-2	5.29	1.97	.063	CONDUCTIVE POLYPROPYLENE	BLACK

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	JOHN COLE	7/29/92	CABINET AND STORAGE DIVIDERS			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
			A	TA-435	TA-435.DWG	D
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: INCHES	SHEET: 1 OF 1

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.