


1750X




DIMENSIONS:


A	3.786" ±0.063
B	4.049" ±0.125
C	3.175" ±0.063
D	3.148" ±0.063
E	2.522" ±0.063
G	0.215" ±0.010

PRIMARY

2000 Ω CT (Term 4-6)



SECONDARY



ELECTRICAL DATA:

Turns ratio:	10.14 : 1
Inductance	@240V, 50Hz => 50.93H (Open circuit)
DCR	@ 20C, PIN #4 - PIN #12 = 5.03 Ω ±20%
	@ 20C, PIN #2 - PIN #6 = 12.30 Ω ±20%
	@ 20C, PIN #2 - PIN #12 = 7.16 Ω ±20%
	@ 20C, PIN #23 - PIN #9 = 0.05 Ω ±20%
	@ 20C, PIN #9 - PIN #21 = 0.02 Ω ±20%
	@ 20C, PIN #21 - PIN #16 = 0.03 Ω ±20%
	@ 20C, PIN #16 - PIN #14 = 0.05 Ω ±20%
FREQ. RESP	@ 100W (447.2V), 50Hz - 12kHz, pin 4 - Pin 6 ±1db (1kHz Ref.)
Pri. Impedance	2000 Ω CT (Term 4-6) Center tap Term 2
Sec. Impedance	2Ω (14V 7.07A) / 4Ω (20V 5A) / 8Ω (28.28V 3.536A)
Power	100 WATTS



**HAMMOND
ELECTRONICS**

52 RANKIN PLACE,
WATERLOO, ONTARIO, N2L 3Z5.

PHONE (519) 886-6181
FAX # (519) 886-9540

TITLE

OUTPUT TRANSFORMER

1	07/28/11	correct primary data	DH	DR BY IOAN POP
0	05/11/09	PRELIMINARY.	I.P.	DATE 05/11/09
NO	DATE	REVISION		DIM IN(X)MM()

1750X