




SFP Modules 100Base-FX LC



ETHERNET via fiber optic cables offers a multitude of advantages for industrial applications. High immunity to interference, electrical isolation, and long ranges are important parameters here.

Description			Item no.	Pack. unit
SFP Module 2: 1310nm, 100Base-FX Multi-mode LC, 2 km	Connector	Duplex LC,	852-201/107-002	1
	Wavelength	1310 nm,		
	Fiber type	Multi-mode 62.5/125 µm, 50/125 µm,		
	Maximum distances	2000 m,		
	Operating temperature	0 °C ... +60 °C,		
	Storage temperature	-20 °C ... +80 °C,		
	Dimensions (mm) W x H x D:	13.4 x 13.3 x 56.6;		
	Laser	Class 1 acc. to EN 60825-1		
SFP Module 30: 1310nm, 100Base-FX Single-mode LC, 30 km	Connector	Duplex LC,	852-201/107-030	1
	Wavelength	1310 nm,		
	Fiber type	Single-mode 9/125 µm,		
	Maximum distances	30000 m,		
	Operating temperature	0 °C ... +60 °C,		
	Storage temperature	-20 °C ... +80 °C,		
	Dimensions (mm) W x H x D:	13.4 x 13.3 x 56.6;		
	Laser	Class 1 acc. to EN 60825-1		

- Characteristics:**
- Duplex LC optical connector
 - Industry standard small form pluggable (SFP) package
 - Compliant with Fast ETHERNET standard;
 - Differential LVPECL inputs and outputs;
 - Single 3.3V power supply;
 - TTL signal detect indicator;
 - Hot pluggable capability