






ID	QTY	PART	DRAWING	DESCRIPTION
1	1	6012	6012	60 SHORT HALF DETAIL
2	1	6013	6013	RIVET STEEL
3	1	6016	6016	TOSION SPRING
4	1	6011	6011	60 LONG WITH U-BARREL DETAIL

8/17/00 REPLACE DWG 60-B-000-A 8/92

NOTES:
 1 DIMENSIONS NOT TOLERANCED ARE FOR REFERENCE.
 2 SPRING FORCE IS TO BE TESTED PER FED SPEC WC440B AT HALF SPREAD. MINIMUM 4.40LBS. @ 5/32"
 3 10 AMP NOMINAL CURRENT CAPACITY



VENDOR BLOCK		 MUELLER ELECTRIC CO. 1583 E. 31st ST. CLEVELAND, OH 44114	
THE VENDOR LISTED BELOW AGREES TO PROVIDE MUELLER ELECTRIC INC. WITH THE AGREED PRODUCT TO THE SPECIFICATIONS OF THIS PRINT. NO CHANGES WILL BE MADE WITHOUT THE APPROVAL OF MUELLER ELECTRIC INC.		SCALE: 1.000 DWG DATE: 8/17/2000 REV DATE:	APPROVED BY: DRAWN BY: SER EDITED BY: REVISION:
COMPANY: _____ REP: _____ TITLE: _____ DATE: _____		PART NUMBER: BU-60U DESCRIPTION: 60 WITH U-BARREL CLIP ASSEMBLY	TOLERANCE: X.X = ±0.1 X.XX = ±0.01 X.XXX = ±0.005 X° = ±0.5°
THIS DRAWING AND THE INFORMATION THERE IN IS THE PROPERTY OF THE MUELLER ELECTRIC COMPANY AND MAY BE USED SOLELY FOR THE PROPOSE FOR WHICH IT IS SUBMITTED. IT IS TO BE TREATED IN CONFIDENCE. IT MAY NOT BE CIRCULATED, REPRODUCED OR DIVULGE TO OTHER PARTIES WITHOUT WRITTEN CONSENT OF MUELLER ELECTRIC INC. IT MUST BE RETURNED UPON REQUEST.		DRAWING NUMBER: 6002	SHEET NO. 1 / 1