


LOC		DIST		REVISIONS						
P	LTR	DESCRIPTION				DATE	DWN	APVD		
	C	REVISED PER ECO 13-001843.				08FEB2013	MGM	CT		

D


C

B


A





SINGLE POLARIZATION



DOUBLE POLARIZATION



THREE KEY POLARIZATION



D

C

B

A

1 THE PART IS MARKED WITH THE TE PART NUMBER, CHINA, DATE CODE AND LOT ID.

2. DWV RATING: 725VAC @ SEA LEVEL


3. WORKING TEMPERATURE: -55°C ~ +125°C

4 MATERIAL:
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
INSULATOR : PEEK
O RING : SILICON RUBBER


5 FINISH
CONTACT: GOLD OVER NICKEL
SHELL : BLACK CHROMIUM

6. WATER PROOF: 1M IMMERSION.

7 ALL TOLERANCES TO BE ±0.20MM UNLESS NOTED.



CAVITY IDENTIFICATION WHEN VIEWED FROM REAR OF CONNECTOR



PANEL CUTOUT

CHROMIUM-BLACK	THREE	SOLDERING	2.54	Ø0.5	15.45	Ø14	M14X1	Ø18	2	2157375-3
CHROMIUM-BLACK	DOUBLE	SOLDERING	2.54	Ø0.5	15.45	Ø14	M14X1	Ø18	2	2157375-2
CHROMIUM-BLACK	SINGLE	SOLDERING	2.54	Ø0.5	15.45	Ø14	M14X1	Ø18	2	2157375-1
FINISH	POLARIZATION	TERMINATION	N	d	L	T	M THREAD	D	SHELL SIZE	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN C.C THOMAS 24FEB2011	TE Connectivity				
DIMENSIONS: mm				CHK R. GROSS 24FEB2011					
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD R. GROSS 24FEB2011	NAME				
0 PLC ± - 7 1 PLC ± - 2 PLC ± 0.20 3 PLC ± - 4 PLC ± - ANGLES ± 3°				PRODUCT SPEC	CIRCULAR HD RECEPTACLE WITH SOCKET CONTACTS JAM NUT, FRONT MOUNTING, STRAIGHT PCB				
MATERIAL 4				APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO				
FINISH 5				WEIGHT -	A2 00779 C=2157375				
CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1 REV C				