


PRODUCT NUMBER
SEE SHEET 3



2.35

10 9 8 7 6 5 4 3 2 1

EVEN COLUMN, CONTACT ROW ID
ODD AND EVEN COLUMNS ARE OFFSET

COLUMN ID

ODD COLUMN, CONTACT ROW ID

TOP SURFACE
OF DAUGHTER
CARD

2.25

(1.50)

(11.05)

(4.45)

10.50 OF EVEN COLUMNS
10.60 OF ODD COLUMNS

1.4

(25.80)

HOUSING


NOTE 5

IMLA A

RETAINER

11.55

90X 1.60 ± 0.15

spec ref		---		dr		Lin-Soe Ngwe		2013/02/21		projection 		size A2		scale 1:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Jerry Ren		2015/02/04				ecn no ELX-DG-20165-1		rel level Released	
ASME Y14.5M				chr		-		-		product family AirMax VSE					
				appr		Collins Lu		2015/02/06							
surface 		linear				title		AIRMAX VS2 R.A. RECEPTACLE ASS'Y, 3 PAIR, 90 POS, 10 IMLA, 20MM		dwg no 10124420		rev B			
														0.X ±.3	
														0.XX ±.10	
		0.XXX ±.050													
		angular		0° ±°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 1 of 3	


PDS: Rev :B

STATUS:Released


Printed: Feb 06, 2015



Copyright FCI.



Copyright FCI.
FCI

spec ref			---		dr		Lin-Soe Ngwe		2013/02/21		projection				MM		size		A2		scale		1:1							
tolerance std			ASME Y14.5M			eng		Jeny Ren		2015/02/04						ecn no		ELX-DG-20165-1												
TOLERANCES UNLESS OTHERWISE SPECIFIED			chr		-		-		-		rel level																			
			appr		Collins Lu		2015/02/06		product family						AirMax VSE						Released									
surface 			linear		0.X		±.3				title		AIRMAX VS2 R.A. RECEPTACLE ASS'Y, 3 PAIR, 90 POS, 10 IMLA, 20MM										dwg no		10124420		rev		B	
					0.XX		±.10																							
					0.XXX		±.050																							
			angular		0°		±°		www.fci.com		cat. no.		-		Product - Customer Drw										sheet 2 of 3					

