


# SPECIFICATIONS

**Model Number:** MX2B3  
**Part Number:** 028422

June 20, 2006



## Mechanical Drawing:



## Motor:

Nominal Voltage	= 115 VAC
Frequency	= 50 / 60 Hz
Nominal Running Current	= 0.20 / 0.18 amps
Locked Rotor Current	= 0.26 / 0.24 amps
Running Power	= 17 / 15 watts
Average Speed	= 2700 / 3100 RPM
Bearings	= Ball
Air Flow	= 98 / 115 CFM
Acoustic	= 45.7 / 49.8 dBA

## Construction:

Venturi: Zinc Alloy, Black  
 Propeller: Plastic, Black, UL 94V-0

## Life Expectancy:

This fan is designed for continuous duty life of 83,000 hours at 40°C.

## Additional Features:

Shaded Pole Induction Motor  
 Impedance Protected  
 Feathered Edge Propeller  
 Operating Temperature: -28°C to 70°C  
 Storage Temperature: -40°C to 85°C  
 Exhaust through propeller

## Termination:

0.120" Wide Terminals

## Agency Approvals:

UL, CSA, VDE, CE