

DE5LC40

400V 5A


FEATURES

- SMT
- Low noise
- trr50ns

APPLICATION

- Switching power supply
- DC/DC converter
- Free Wheel
- Home Appliances, Office Equipment
- Telecommunication, Factory Automation

OUTLINE DIMENSIONS



RATINGS

●Absolute Maximum Ratings (If not specified Tc=25°C)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-55~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		400	V
Average Rectified Forward Current	Io	50Hz sine wave, R-load, Rating for each diode Io/2, Tc=61°C	5	A
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=25°C	50	A

●Electrical Characteristics (If not specified Tc=25°C)


Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=2.5A, Pulse measurement, Rating of per diode	Max.1.3	V
Reverse Current	IR	VR=VRM, Pulse measurement, Rating of per diode	Max.10	μA
Reverse Recovery Time	trr	IF=0.5A, IR=1A, Rating of per diode	Max.50	ns
Thermal Resistance	θjc	junction to case	Max.12	°C/W
	θja	junction to ambient	Max.55	°C/W

DE5LC40


Forward Voltage



DE5LC40 Forward Power Dissipation




$T_j = 150^\circ\text{C}$




DE5LC40

Derating Curve




$$V_R = V_{RM}$$




DE5LC40

Derating Curve




$$V_R = V_{RM}$$




DE5LC40

Derating Curve




$$V_R = V_{RM}$$



DE5LC40

Peak Surge Forward Capability



DE5LC40 Junction Capacitance

