




- 1 PARTS MUST COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- 2 MATES WITH HOUSING NO. 350736 USING SOCKET CONTACTS.
- 3 CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 [$.000050$] NICKEL, THEN STRIPED WITH 0.00076 [$.000030$] GOLD IN CONTACT AREA INDICATED AND TIN-LEAD ON SOLDER TAIL END.
- 4 CONTACT IS PLATED OVERALL WITH 0.00127 [$.000050$] NICKEL, THEN 0.00076 [$.000030$] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 6 SUPERSEDED BY 641976-4

PH BRZ GOLD 4		NYLON, UL94V-0	641976-4
PH BRZ GOLD 3		NYLON, UL94V-0	641976-2
PH BRZ TIN		NYLON, UL94V-0	641976-1
CONTACT		HOUSING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER CHK S. RIDGILL APP'D S. RIDGILL	14OCT2005 19-NOV-2003 19-NOV-2003
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	HEADER ASSEMBLY, PIN, POLARIZED, UNIVERSAL MATE-N-LOK(TM), 15 CIRCUIT
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES	$\pm$ $\pm$ $\pm$ $\pm$ $\pm$ $\pm$	APPLICATION SPEC	SIZE A1
MATERIAL SEE CHART	FINISH	WEIGHT	CAGE CODE 00779
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1