

LOC		DIST		REVISIONS					
-		-		DESCRIPTION			DATE	DWN	APVD
		P	LTR						
			F	REV PER ECO 14-003443			3-21-14	CT	DH

D

C

B



A

D



C

B

A



- 1 HOUSING: LCP, UL94V0, COLOR: BLACK. CONTACT: PHOSPHOR BRONZE.
- 2 FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN. TIN-LEAD ON PCB TAIL OVER 3.81µm MIN. NICKEL OVER ALL.
- 3 FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN. TIN ON PCB TAIL OVER 3.81µm MIN. NICKEL OVER ALL.
- 4 PLATE THROUGH HOLE PER TE SPEC. 114-13056 FIGURE 4.
- 5 ADDITIONAL CONNECTOR-SIDE KEEPOUT AREA REQUIRED IF CONNECTOR-SIDE EXTRACTION TOOL IS TO BE USED.







PC BOARD LAYOUT
(CONNECTOR SIDE)
(SEE SHEET 2 FOR RTM)
SCALE 5:1

3	1410140-2
2	1410140-1
PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TREA 08NOV2002	TE Connectivity	
DIMENSIONS:		CHK J. CONSOLI 18NOV2002		
mm		APVD J. CONSOLI 18NOV2002	NAME	
		PRODUCT SPEC	CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, CENTER, 20.3mm, MultiGig RT 2	
		108-2072		
		APPLICATION SPEC		
		114-13056		
MATERIAL		WEIGHT	SIZE	
FINISH			CAGE CODE	
CUSTOMER DRAWING			DRAWING NO	
			RESTRICTED TO	
			A100779C=1410140	
			SCALE 2:1	
			SHEET 1 OF 2	
			REV F	

REAR TRANSITION MODULE APPLICATION



RTM PC BOARD LAYOUT
(CONNECTOR SIDE)
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. TREA	08NOV02002	 TE Connectivity
		CHK J. CONSOLI	18NOV02002	
		APPD	18NOV02002	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, CENTER, 20.3mm, MultiGig RT 2
		Ø PLC ±.1 PLC ±0.5 PLC ±0.13 PLC ±.1 PLC ±.1 ANGLES ±10°		
MATERIAL - FINISH		WEIGHT -		
-		-		
-		-		
		CUSTOMER DRAWING		SIZE CAGE CODE DRAWING NO A100779C1410140
		SCALE 2:1 SHEET 2 OF 2 REV F		RESTRICTED TO