


13		12		11		10		9		8		7		6		5		4		3		2		1		
CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"		CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"		CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"	
			MM	IN.	MM	IN.	MM	IN.				MM	IN.	MM	IN.	MM	IN.				MM	IN.				
08	25-02-3008	0771	7,62	.300	17,78	.700	20,32	.800	42	25-02-3042	0788	50,80	2.000	60,96	2.400	63,50	2.500									
10	25-02-3010	0772	10,16	.400	20,32	.800	22,86	.900	44	25-02-3044	0789	53,34	2.100	63,50	2.500	66,04	2.600									
12	25-02-3012	0773	12,70	.500	22,86	.900	25,40	1.000	46	25-02-3046	0790	55,88	2.200	66,04	2.600	68,58	2.700									
14	25-02-3014	0774	15,24	.600	25,40	1.000	27,94	1.100	48	25-02-3048	0791	58,42	2.300	68,58	2.700	71,12	2.800									
16	25-02-3016	0775	17,78	.700	27,94	1.100	30,48	1.200	50	25-02-3050	0792	60,96	2.400	71,12	2.800	73,66	2.900									
18	25-02-3018	0776	20,32	.800	30,48	1.200	33,02	1.300	52	25-02-3052	0793	63,50	2.500	73,66	2.900	76,20	3.000									
20	25-02-3020	0777	22,86	.900	33,02	1.300	35,56	1.400	54	25-02-3054	0794	66,04	2.600	76,20	3.000	78,74	3.100									
22	25-02-3022	0778	25,40	1.000	35,56	1.400	38,10	1.500	56	25-02-3056	0795	68,58	2.700	78,74	3.100	81,28	3.200									
24	25-02-3024	0779	27,94	1.100	38,10	1.500	40,64	1.600	58	25-02-3058	0796	71,12	2.800	81,28	3.200	83,82	3.300									
26	25-02-3026	0780	30,48	1.200	40,64	1.600	43,10	1.700	60	25-02-3060	0797	73,66	2.900	83,82	3.300	86,36	3.400									
28	25-02-3028	0781	33,02	1.300	43,10	1.700	45,72	1.800	62	25-02-3062	0798	76,20	3.000	86,36	3.400	88,90	3.500									
30	25-02-3030	0782	35,56	1.400	45,72	1.800	48,26	1.900	64	25-02-3064	0799	78,74	3.100	88,90	3.500	91,44	3.600									
32	25-02-3032	0783	38,10	1.500	48,26	1.900	50,80	2.000	66	25-02-3066	0800	81,28	3.200	91,44	3.600	93,98	3.700									
34	25-02-3034	0784	40,64	1.600	50,80	2.000	53,34	2.100	68	25-02-3068	0801	83,82	3.300	93,98	3.700	96,52	3.800									
36	25-02-3036	0785	43,10	1.700	53,34	2.100	55,88	2.200	70	25-02-3070	0802	86,36	3.400	96,52	3.800	99,06	3.900									
38	25-02-3038	0786	45,72	1.800	55,88	2.200	58,42	2.300	72	25-02-3072	0803	88,90	3.500	99,06	3.900	101,60	4.000									
40	25-02-3040	0787	48,26	1.900	58,42	2.300	60,96	2.400																		

3° MAX. ROTATION
PERMISSIBLE


DETAIL "V"

SCALE = 20:1


DETAIL "S"





DETAIL "V"
SCALE = 20:1



DETAIL "S"



SECTION W-W



- NOTES:
1. WAFER MATERIAL: GLASS FILLED NYLON; COLOR: BLACK
 2. PIN MATERIAL: COPPER ALLOY
 3. PIN PLATING:
TIP: 15 MICROINCHES MINIMUM GOLD IN SELECTED AREA
TAIL: 75 MICROINCHES MINIMUM TIN IN SELECTED AREA
OVER NICKEL UNDERPLATE OVER-ALL
 4. PINS MUST MEET SOLDERABILITY SPEC. NO. 152
 5. PIN PUSH-OUT FORCE (1.81 KG)/4 LBS MINIMUM
 6. REFER TO P.S. NO. 70204
 7. STANDARD PACKAGING PER: PK-70873-0070

CORRECT DIMENSION EC NO: UCP2011-3892 DRWN:MS BARRA 2011/06/27 CHKD:MORGAN APPR:SMILLER 2011/07/07	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY JAS	DATE 1986/05/20	TITLE SHROUDED HEADER DUAL ROW W/PCB SLOTS & GUIDE EARS .100 GRID, .025 SQ PIN	
			4 PLACES	± ---	± ---	CHECKED BY EIK	DATE 1986/05/20		
			3 PLACES	± ---	± .010				
			2 PLACES	± 0.25	± ---	APPROVED BY WAZ	DATE 1986/05/20	DOCUMENT NO. SDA-70204-0769-0832	
			1 PLACE	± ---	± ---				
			ANGULAR ±1/2°			MATERIAL NO.	SEE TABLE		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					