






LOC		DIST		REVISIONS						
CM		53		P	LTR	DESCRIPTION		DATE	DWN	APVD
					U1	REVISED PER ECO-11-004917		11MAR11	RK	HMR


 NICKEL OVER ENTIRE TERMINAL WITH 0.00076 THICK GOLD OVER 5.08 LENGTH.



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1




SECTION C-C
SCALE 10:1

1.50	.059	2.41	.095	-	-
1.27	.050	2.29	.090	16.89	.665
0.76	.030	2.16	.085	5.08	.200
0.20	.008	2.08	.082	3.68	.145
0.13	.005	1.91	.075	3.30	.130
0.00076	0.00030	1.57	.062	2.79	.110
MM	IN	MM	IN	MM	IN

CONVERSION TABLE

PRE-TIN	0.20 PH BRZ	1.27 - 2.79	0.2 - 0.9 mm ² (24-18 AWG)	350629-8
	0.20 BRASS	1.27 - 2.79	0.2 - 0.9 mm ² (24-18 AWG)	350629-5
PRE-TIN	0.20 BRASS	1.27 - 2.79	0.2 - 0.9 mm ² (24-18 AWG)	350629-1
FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 9-12-90	 TE Connectivity	
		CHK R. SWING 9-13-90		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME .062 PIN, COMMERCIAL PIN AND SOCKET	
		0. PLC ± -	APVD C. CASH 9-27-90	
		1. PLC ± -		
		2. PLC ± -	PRODUCT SPEC	
		3. PLC ± 0.13		
		4. PLC ± -	APPLICATION SPEC	
		ANGLES ± -		
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT -	
		CUSTOMER DRAWING		SCALE 8:1 SHEET 1 OF 1 REV U1