




HONEYWELL
PART NUMBER
V7-4A33E9-000-2

PRODUCT CODE: CWC3910
SUPERSEDES: X201252-V7

REV	DOCUMENT	CHANGED BY	CHECK
A	0038443	SS 25MAR08	BLR

- NOTES:
- 1 - SWITCH MATERIALS WILL WITHSTAND 150°C
 - 2 - RAW MATERIAL - COMMERCIAL STANDARD

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	SS	25MAR08	Honeywell				
OPERATING FORCE---- 25 GRAMS MAX		CONTACT ARRANGEMENT S P N C				CHECK	BLR	25MAR08					
DIFFERENTIAL TRAVEL---- .002-.010		L162 5A 125, 250, 277 VAC 1/10HP 250 VAC T SE RU		NO PLACES X ± .040		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH, BASIC				
OVERTRAVEL----- .050 MIN				ONE PLACE .X ± .030									
FREE POSITION----- .625 MAX				TWO PLACE .XX ± .015		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY							
RELEASE TRAVEL----- .010 MIN				THREE PLACE .XXX ± .005									
				THIRD ANGLE PROJECTION 					SIZE	TYPE	CAGE CODE	DRAWING NAME	
							B	I	-	V7-4A33E9-000-2		A	
							Pro/ENGINEER 2D		SCALE	NTS		SHEET 1 OF 1	