

# Cree® 5-mm Round LED

## Model # LC503UYL1-15Q-A

### Data Sheet

15-degree, 5-mm round LED lamp in amber color with water-transparent lens and no stopper

#### Applications

- Advertising Signs
- Indicators
- Traffic Lights
- Automotive Lighting

#### Absolute Maximum Ratings ( $T_A = 25^\circ\text{C}$ )

Items	Symbol	Absolute Maximum Rating	Unit
Forward Current	$I_F$	50	mA
Peak Forward Current <sup>Note</sup>	$I_{FP}$	200	mA
Reverse Voltage	$V_R$	5	V
Power Dissipation	$P_D$	130	mW
Operation Temperature	$T_{opr}$	-40 ~ +95	°C
Storage Temperature	$T_{stg}$	-40 ~ +100	°C
Lead Soldering Temperature	$T_{sol}$	Max. 260°C for 3 sec. max. (3 mm from the base of the epoxy bulb)	
Electrostatic Discharge Classification(MIL-STD-883E)	ESD	Class 2	

**Note:** Pulse width  $\leq 0.1$  msec, duty  $\leq 1/10$ .

#### Typical Electrical & Optical Characteristics ( $T_A = 25^\circ\text{C}$ )

Characteristics	Symbol	Condition	Unit	Minimum	Typical	Maximum
Forward Voltage	$V_F$	$I_F = 20$ mA	V		2.1	2.6
Reverse Current	$I_R$	$V_R = 5$ V	μA			100
Dominant Wavelength	$\lambda_D$	$I_F = 20$ mA	nm	584	591	596
Luminous Intensity	$I_V$	$I_F = 20$ mA	mcd	5860	16000	
50% Power Angle	$2\theta_{1/2H-H}$	$I_F = 20$ mA	deg		15	

## Standard Bins for LC503UYL1-15Q-A ( $I_F = 20$ mA)

Lamps are sorted to luminous intensity ( $I_v$ ) and dominant wavelength ( $\lambda_D$ ) bins shown.

Orders for LC503UYL1-15Q-A may be filled with any or all bins contained as below.

All luminous intensity ( $I_v$ ) and dominant wavelength ( $\lambda_D$ ) values shown and specified are at  $I_F = 20$  mA.

	X2	X3	X4	X5	
Luminous Intensity ( $I_v$ )					Z3 or above
					Z2
23500 mcd					Z1
16800 mcd					Z
12000 mcd					Y
8200 mcd					
5860 mcd					
Dominant Wavelength ( $\lambda_D$ )	584 nm	587 nm	590 nm	593 nm	596 nm

### Important Notes:

1. All ranks will be included per delivery; rank ratio will be based on the dice distribution.
2. Pb content <1000 ppm.
3. Tolerance of measurement of luminous intensity is  $\pm 15\%$ .
4. Tolerance of measurement of dominant wavelength is  $\pm 1$  nm.
5. Tolerance of measurement of  $V_F$  is  $\pm 0.05$  V.
6. Packaging methods are available for selection; please refer to the "Cree LED Lamp Packaging Standard" document.
7. Please refer to the "Cree LED Lamp Reliability Test Standards" document for reliability test conditions.
8. Please refer to the "Cree LED Lamp Soldering & Handling" document for information about how to use this LED product safely.

## Graphs




FIG.1 FORWARD CURRENT VS.  
FORWARD VOLTAGE.




FIG.2 REVERSE CURRENT VS.  
REVERSE VOLTAGE.




FIG.3 RELATIVE LUMINOUS INTENSITY VS.  
FORWARD CURRENT.

Half Power  $\Delta$  WL=20nm  
Domi WL = 591nm




FIG.4 RELATIVE LUMINOUS INTENSITY VS.  
WAVELENGTH.




FIG.5 MAXIMUM FORWARD DC CURRENT VS  
AMBIENT TEMPERATURE ( $T_{jmax}=105^{\circ}\text{C}$ )





FIG.6 FAR FIELD PATTERN

## Mechanical Dimensions

All dimensions are in mm. Tolerance is  $\pm 0.25$  mm unless otherwise noted.

An epoxy meniscus may extend about 1.5 mm down the leads.

Burr around bottom of epoxy may be 0.5 mm max.



## Notes

### RoHS Compliance

The levels of environmentally sensitive, persistent biologically toxic (PBT), persistent organic pollutants (POP), or otherwise restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2002/95/EC on the restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS), as amended through April 21, 2006.


### Vision Advisory Claim

Users should be cautioned not to stare at the light of this LED product. The bright light can damage the eye.

## Kit Number System

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options. Please refer to the "Cree LED Lamp Packaging Standard" document for more information about shipping and packaging options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:



\* Contact your Cree sales representative for ordering information.

## Standard Available Kits\*

Kit Number	Description
LC503UYL1-15Q-A-00001	5mm Round 15 Amber, Full Rank, Bulk Pack
LC503UYL1-15Q-A-00002	5mm Round 15 Amber, IV: Full Rank, Hue: X2-X4, Bulk Pack
LC503UYL1-15Q-A-00003	5mm Round 15 Amber, IV: Full Rank, Hue: X3-X5, Bulk Pack
LC503UYL1-15Q-A-00004	5mm Round 15 Amber, IV: Full Rank, Hue: Consecutive 2 Hue of X2-X4, Bulk Pack
LC503UYL1-15Q-A-00005	5mm Round 15 Amber, IV: Full Rank, Hue: Consecutive 2 Hue of X3-X5, Bulk Pack
LC503UYL1-15Q-A-00011	5mm Round 15 Amber, IV: Z, Z1, Z2, Hue: Full Rank, Bulk Pack
LC503UYL1-15Q-A-00012	5mm Round 15 Amber, IV: Z, Z1, Z2, Hue: X2-X4, Bulk Pack
LC503UYL1-15Q-A-00013	5mm Round 15 Amber, IV: Z, Z1, Z2, Hue: X3-X5, Bulk Pack
LC503UYL1-15Q-A-00014	5mm Round 15 Amber, IV: Z, Z1, Z2, Hue: Consecutive 2 Hue of X2-X4, Bulk Pack
LC503UYL1-15Q-A-00015	5mm Round 15 Amber, IV: Z, Z1, Z2, Hue: Consecutive 2 Hue of X3-X5, Bulk Pack

\* Please contact your Cree representative about the availability of non-standard kits.