



REV.	DATE	ECR NO.	DESCRIPTION
A	09/22/99	—	ADD REFERENCE NO. 51—0838
B	05/14/06	—	MODIFY BODY AND CONTACT PLATING TO BRT. TIN
C	05/20/08	—	REVISE BODY PLATING TO NICKEL, CONTACT PLATING TO MATTE TIN



- NOTE:
- BRIGHT TIN PL. 200 MIN. THICK OVER NICKEL PL. 50 MIN. THICK OVER COPPER PL. 100 MIN. THICK.
 - REF: 51—0838

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex						
8					DRAWN	G.R.S.	05/20/08								
7					CHECKED			PART DESCRIPTION		F SERIES R/A P.C. MOUNT RECEPTACLE —					
6					ISSUED										
5					SHEET	1 OF 1				PART NO. 222131					
4	INSULATOR	DELTRIN	NATURAL	1											
3	CONTACT PIN	BRASS	MATTE TIN	2					PART NO. 222131						
2	INSULATOR	P.P.	NATURAL	1											
1	HOUSING/BODY	BRASS	NICKEL	1					DWG. NO. 222131.DWG				REV. C	SIZE A	SCALE NA
DESCRIPTION				MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING								
								CAD FILE	C:/222/222131.DWG						