

ADSL LINE TRANSFORMERS

For Centillium ADSL CPE Chipsets



- Matched to Centillium's CopperFlite™ CT-L51ST81, Flite Optimizer™ CT-L52SU81, and Universal CopperFlite™ CT-L61ST81 chipsets
- Excellent THD performance in a small footprint
- Designed to meet UL1950 and EN60950 supplementary insulation requirements for working voltages up to 250 Vrms

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Mounting	Turns Ratio ($\pm 2\%$)	Inductance @ 10 kHz, 100 mV	Leakage Inductance @ 100 kHz, 0.1 Vrms
BX2258	SMT	1CS:1CS (1-5) : (7-10) with (2-4) & (8-9) Shorted	5.0 mH $\pm 10\%$ (7-10) with (8-9) Shorted	15 μ H Max (1-2) with (4-5), (7-10), & (8-9) Shorted
BX2259	SMT	1CS:2.125CS (1-4) : (6-10) with (2-3) & (7-9) Shorted	5.0 mH $\pm 10\%$ (6-10) with (7-9) Shorted	10 μ H Max. (9-10) with (1-4), (2-3), & (6-7) Shorted
BX2353	SMT	1CS:2.125CS (1-4) : (7-10) with (2-3) & (8-9) Shorted	5.0 mH $\pm 10\%$ (7-10) with (8-9) Shorted	13 μ H Max. (7-10) with (1-4), (2-3), & (8-9) Shorted
BX2358	SMT	1CS:1CS (1-4) : (7-10) with (2-3) & (8-9) Shorted	5.0 mH $\pm 10\%$ (7-10) with (8-9) Shorted	15 μ H Max. (7-10) with (1-4), (2-3), & (8-9) Shorted

Additional Electrical Specifications

Part Number	Longitudinal Balance (from 30 kHz to 1.1 MHz)	THD at 100 Ω (@ 30 kHz, 2.5 Vrms)	DC Resistance		Isolation Voltage (1 sec)
BX2258	≤ -40 dB	≤ -85 dB	1.3 Ω MAX (1-2) 1.6 Ω MAX (4-5)	1.5 Ω MAX (7-9) = (8-10)	1,875 Vrms
BX2259	≤ -40 dB	≤ -85 dB	0.35 Ω MAX (1-3) 0.40 Ω MAX (2-4)	1.75 Ω MAX (6-7) = (9-10)	1,875 Vrms
BX2353	≤ -40 dB	≤ -85 dB	0.35 Ω MAX (1-3) 0.40 Ω MAX (2-4)	1.75 Ω MAX (7-9) = (8-10)	1,875 Vrms
BX2358	≤ -40 dB	≤ -85 dB	1.0 Ω MAX (1-3) 1.3 Ω MAX (2-4)	1.1 Ω MAX (7-9) = (8-10)	1,875 Vrms

NOTE: Transformers are shipped in trays unless Tape & Reel packaging is specified by adding the suffix "T" to the part number (i.e. BX2258T).

ADSL LINE TRANSFORMERS


For Centillium ADSL CPE Chipsets




Mechanical

Schematics


BX2XXX




BX2258



BX2259



BX2353/BX2358



Weight6.2 grams

Tape & Reel150/reel

Tray60/tray

Dimensions: $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
<http://www.pulseeng.com>
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 287 8998
FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

HONG KONG (China/Hong Kong)

19/F, China United Plaza
1008 Tai Nan West Street
Cheung Sha Wan, Kowloon
Hong Kong, China
TEL: 852 2788 6588
FAX: 852 2776 1055

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.