







SECTION K-K'



LEGEND

SD-35362-***

CTK NO. COLOR

0 : NATURAL
1 : BLACK
2 : RED
3 : YELLOW
4 : BLUE
5 : GREEN

6 : TUBE PACKING (Natural Color)
7 : TUBE PACKING (Red Color)
8 : TUBE PACKING (Blue Color)

FINAL GOOD (BULK)
5 : SELECTIVE KINK (LEAD FREE)
6 : NONE KINK (LEAD FREE)


SUB ASSY (TUBE)
7 : SELECTIVE KINK (LEAD FREE)
8 : NONE KINK (LEAD FREE)

NOTES

1. MATERIAL : UNFILLED POLYAMIDE, UL94V-0
PIN : BRASS, TIN PLATED
2. FINISHES : PIN : Sn 3-5μm OVERALL
3. PRODUCT SPECIFICATION : PS-35507-003
4. MATING HOUSING : 35507-***0*
MATING TERMINAL : 50212-8000
5. KINK

CTK NO	1	2	3	4	5	N-2	N-1	N
6 CTK OVER	-	A	B	-	-	B	A	-
5 CTK	A	B	-	B	A			
4 CTK	A	B	B	A				

31.3	28	32.3	3536215**	35362-15**	15
29.3	26	30.3	3536214**	35362-14**	14
27.3	24	28.3	3536213**	35362-13**	13
25.3	22	26.3	3536212**	35362-12**	12
23.3	20	24.3	3536211**	35362-11**	11
21.3	18	22.3	3536210**	35362-10**	10
19.3	16	20.3	3536209**	35362-09**	9
17.3	14	18.3	3536208**	35362-08**	8
15.3	12	16.3	3536207**	35362-07**	7
13.3	10	14.3	3536206**	35362-06**	6
11.3	8	12.3	3536205**	35362-05**	5
9.3	6	10.3	3536204**	35362-04**	4
(C)	B	(A)	ENG. NO.	ENG. NO.	CTK



LEAD FREE	
30 over	±0.3
10 over 30 under	±0.25
10 under	±0.2
ANGLE	±3°
GENERAL TOLERANCE	

REVISED
EC NO: KOR2014-0116
DRW:KTKIM01 2014/04/15
CHKD: CHYKD
APPR:YSKIM02 2014/04/21

QUALITY SYMBOLS
F_A=0
F_G=0
F_P=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES	± --- ± ---
3 PLACES	± --- ± ---
2 PLACES	± --- ± ---
1 PLACE	± --- ± ---
0 PLACE	± ±
ANGULAR ± --- °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
YSOOKIM	1996/09/11
CHECKED BY	DATE
YSOOKIM	1996/09/11
APPROVED BY	DATE
MATERIAL NO.	
SEE TABLE	
SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE 5:1

DESIGN UNITS METRIC

THIRD ANGLE PROJECTION

2.0 W/B WAFER ASS'Y -LEAD FREE-

molex

SD-35362-002

SHEET NO. 1 OF 3

10

9

8

7

6






5

4

3

2


1



NOTES

1. MATERIAL : TUBE - TRANSLUCENT P.V.C (P-1000)
Wafer - POLYAMIDE, UL94V-0
PIN - BRASS SQ 0.5mm
2. BOW(CAMBER) : 1.0mm MAX/Total Length
3. DIMENSIONS GIVEN ACROSS CENTER LINES ARE SYMMETRICAL ABOUT THOSE CENTER LINES WITH HALF THE TOTAL LENGTH.
4. TOTAL TUBE LENGTH : 560mm ± 1mm
5. TWIST : 5° MAX./Total Length
6. BURRS : 0.2mm MAX.
7. SKEW : PRODUCTS MUST BE FLOWED SMOOTHLY WHEN THIS STICK IS PLACES 30° ANGLE.
8. THICKNESS : 0.6mm ± 0.1mm
9. ARTWORK : PER E-35900-0434 (SILK SCREEN COLOR : RED)
10. APPLICABLE STOPPER(RUBBER) : 35900-0435

TABLE



10		20**	-20**	20
10		19**	-19**	19
10		18**	-18**	18
10		17**	-17**	17
15		16**	-16**	16
15		15**	-15**	15
15		14**	-14**	14
15		13**	-13**	13
15		12**	-12**	12
20		11**	-11**	11
20		10**	-10**	10
25		09**	-09**	9
25		08**	-08**	8
30		07**	-07**	7
35		06**	-06**	6
40		05**	-05**	5
50		04**	-04**	4
60		03**	-03**	3
70	3536202**	35362-02**		2
QT'y	Material NO.	ENG. NO.		CKT



KINK TABLE(FOR 35362-****)

CKT NO	1	2	3	4	5	N-2	N-1	N
6 CKT OVER	-	A	B	-	-	B	A	-
5 CKT	A	B	-	B	A			
4 CKT	A	B	B	A				
3 CKT	A	B	A					
2 CKT	None Kink							

** 35362-0287 IS ONLY KINKED 2P

CKT NO	1	2
PRODUCT NO.		
35362-0287	A	B

LEAD FREE

REVISED EC NO: KOR2014-0116 DRWN:KTK1M01 2014/04/14 CHKD: APPR:YSK1M02 2014/04/21	DESCRIPTION	QUALITY SYMBOLS F_A=0 F_C=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 			
			4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE 2.0 W/B WAFER ASS'Y TUBE PACKING -LEAD FREE-				
			3 PLACES	± ---	± ---	CHECKED BY	DATE					
			2 PLACES	± ---	± ---	JKOH	2000/12/11	molex				
			1 PLACE	± 0.2	± ---	APPROVED BY	DATE					
			0 PLACE	± ---	±							
			ANGULAR ± 1 °			MATERIAL NO.		DOCUMENT NO.			SHEET NO.	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			9999999999		SD-35362-003			1 OF 1	
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

9

8

7

6

5

4

3

2

1