

MCR100 Series

Preferred Device

Sensitive Gate Silicon Controlled Rectifiers

Reverse Blocking Thyristors

PNPN devices designed for high volume, line-powered consumer applications such as relay and lamp drivers, small motor controls, gate drivers for larger thyristors, and sensing and detection circuits. Supplied in an inexpensive plastic TO-226AA package which is readily adaptable for use in automatic insertion equipment.

Features

- Sensitive Gate Allows Triggering by Microcontrollers and Other Logic Circuits
- Blocking Voltage to 600 V
- On-State Current Rating of 0.8 Amperes RMS at 80°C
- High Surge Current Capability – 10 A
- Minimum and Maximum Values of IGT, VGT and IH Specified for Ease of Design
- Immunity to dV/dt – 20 V/ μ sec Minimum at 110°C
- Glass-Passivated Surface for Reliability and Uniformity
- Pb-Free Packages are Available*




ON Semiconductor®

<http://onsemi.com>


SCRs
0.8 A RMS
100 thru 600 V



MARKING DIAGRAM



TO-92 (TO-226)
CASE 029
STYLE 10



x = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week

PIN ASSIGNMENT

PIN ASSIGNMENT	
1	Cathode
2	Gate
3	Anode

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

Preferred devices are recommended choices for future use and best overall value.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MCR100 Series

ORDERING INFORMATION

Device	Package Code	Shipping [†]
MCR100-003	TO-92 (TO-226)	5000 Units / Bulk
MCR100-004		
MCR100-006		
MCR100-008		
MCR100-3RL		
MCR100-6RL		2000 Units / Tape & Reel
MCR100-6RLRA		2000 Units / Tape & Ammunition Box
MCR100-6RLRM		
MCR100-6ZL1		2000 Units / Tape & Reel
MCR100-8RL		
MCR100-003G	TO-92 (TO-226) (Pb-Free)	5000 Units / Bulk
MCR100-006G		
MCR100-008G		
MCR100-3RLG		2000 Units / Tubes
MCR100-6RLG		2000 Units / Tape & Reel
MCR100-6RLRAG		
MCR100-6RLRMG		2000 Units / Tape & Ammunition Box
MCR100-6ZL1G		2000 Units / Tape & Reel
MCR100-8RLG		

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Peak Repetitive Off-State Voltage (Note 1) (T _J = -40 to 110°C, Sine Wave, 50 to 60 Hz; Gate Open)	V _{DRM} , V _{RRM}		V
MCR100-3		100	
MCR100-4		200	
MCR100-6		400	
MCR100-8		600	
On-State RMS Current, (T _C = 80°C) 180° Conduction Angles	I _{T(RMS)}	0.8	A
Peak Non-Repetitive Surge Current, (1/2 Cycle, Sine Wave, 60 Hz, T _J = 25°C)	I _{TSM}	10	A
Circuit Fusing Consideration, (t = 8.3 ms)	I ² t	0.415	A ² s
Forward Peak Gate Power, (T _A = 25°C, Pulse Width ≤ 1.0 μs)	P _{GM}	0.1	W
Forward Average Gate Power, (T _A = 25°C, t = 8.3 ms)	P _{G(AV)}	0.10	W
Forward Peak Gate Current, (T _A = 25°C, Pulse Width ≤ 1.0 μs)	I _{GM}	1.0	A
Reverse Peak Gate Voltage, (T _A = 25°C, Pulse Width ≤ 1.0 μs)	V _{GRM}	5.0	V
Operating Junction Temperature Range @ Rate V _{RRM} and V _{DRM}	T _J	-40 to 110	°C
Storage Temperature Range	T _{stg}	-40 to 150	°C

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

1. V_{DRM} and V_{RRM} for all types can be applied on a continuous basis. Ratings apply for zero or negative gate voltage; however, positive gate voltage shall not be applied concurrent with negative potential on the anode. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.

MCR100 Series

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Case Junction-to-Ambient	$R_{\theta JC}$ $R_{\theta JA}$	75 200	$^{\circ}\text{C}/\text{W}$
Lead Solder Temperature ($< 1/16''$ from case, 10 secs max)	T_L	260	$^{\circ}\text{C}$

ELECTRICAL CHARACTERISTICS ($T_C = 25^{\circ}\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
----------------	--------	-----	-----	-----	------

OFF CHARACTERISTICS

Peak Repetitive Forward or Reverse Blocking Current (Note 2) ($V_D = \text{Rated } V_{DRM} \text{ and } V_{RRM}; R_{GK} = 1 \text{ k}\Omega$)	I_{DRM}, I_{RRM}	– –	– –	10 100	μA
$T_C = 25^{\circ}\text{C}$ $T_C = 110^{\circ}\text{C}$					

ON CHARACTERISTICS

Peak Forward On-State Voltage* ($I_{TM} = 1.0 \text{ A Peak @ } T_A = 25^{\circ}\text{C}$)	V_{TM}	–	–	1.7	V
Gate Trigger Current (Continuous dc) (Note 3) ($V_{AK} = 7.0 \text{ Vdc}, R_L = 100 \Omega$)	I_{GT}	–	40	200	μA
Holding Current ⁽²⁾ ($V_{AK} = 7.0 \text{ Vdc}$, Initiating Current = 20 mA)	I_H	– –	0.5 –	5.0 10	mA
Latch Current ($V_{AK} = 7.0 \text{ V}$, $I_g = 200 \mu\text{A}$)	I_L	– –	0.6 –	10 15	mA
Gate Trigger Voltage (Continuous dc) (Note 3) ($V_{AK} = 7.0 \text{ Vdc}, R_L = 100 \Omega$)	V_{GT}	– –	0.62 –	0.8 1.2	V
$T_C = 25^{\circ}\text{C}$ $T_C = -40^{\circ}\text{C}$					

DYNAMIC CHARACTERISTICS

Critical Rate of Rise of Off-State Voltage ($V_D = \text{Rated } V_{DRM}$, Exponential Waveform, $R_{GK} = 1000 \Omega, T_J = 110^{\circ}\text{C}$)	dV/dt	20	35	–	$\text{V}/\mu\text{s}$
Critical Rate of Rise of On-State Current ($I_{PK} = 20 \text{ A}$; $P_w = 10 \mu\text{sec}$; $di/dt = 1 \text{ A}/\mu\text{sec}$, $I_{gt} = 20 \text{ mA}$)	di/dt	–	–	50	$\text{A}/\mu\text{s}$


*Indicates Pulse Test: Pulse Width $\leq 1.0 \text{ ms}$, Duty Cycle $\leq 1\%$.

2. $R_{GK} = 1000 \Omega$ included in measurement.

3. Does not include R_{GK} in measurement.

Voltage Current Characteristic of SCR

Symbol	Parameter
V_{DRM}	Peak Repetitive Off State Forward Voltage
I_{DRM}	Peak Forward Blocking Current
V_{RRM}	Peak Repetitive Off State Reverse Voltage
I_{RRM}	Peak Reverse Blocking Current
V_{TM}	Peak on State Voltage
I_H	Holding Current



MCR100 Series




Figure 1. Typical Gate Trigger Current versus Junction Temperature




Figure 2. Typical Gate Trigger Voltage versus Junction Temperature




Figure 3. Typical Holding Current versus Junction Temperature




Figure 4. Typical Latching Current versus Junction Temperature




Figure 5. Typical RMS Current Derating




Figure 6. Typical On-State Characteristics

MCR100 Series

TO-92 EIA RADIAL TAPE IN FAN FOLD BOX OR ON REEL




Figure 7. Device Positioning on Tape

Symbol	Item	Specification			
		Inches		Millimeter	
		Min	Max	Min	Max
D	Tape Feedhole Diameter	0.1496	0.1653	3.8	4.2
D2	Component Lead Thickness Dimension	0.015	0.020	0.38	0.51
F1, F2	Component Lead Pitch	0.0945	0.110	2.4	2.8
H	Bottom of Component to Seating Plane	.059	.156	1.5	4.0
H1	Feedhole Location	0.3346	0.3741	8.5	9.5
H2A	Deflection Left or Right	0	0.039	0	1.0
H2B	Deflection Front or Rear	0	0.051	0	1.0
H4	Feedhole to Bottom of Component	0.7086	0.768	18	19.5
H5	Feedhole to Seating Plane	0.610	0.649	15.5	16.5
L	Defective Unit Clipped Dimension	0.3346	0.433	8.5	11
L1	Lead Wire Enclosure	0.09842	—	2.5	—
P	Feedhole Pitch	0.4921	0.5079	12.5	12.9
P1	Feedhole Center to Center Lead	0.2342	0.2658	5.95	6.75
P2	First Lead Spacing Dimension	0.1397	0.1556	3.55	3.95
T	Adhesive Tape Thickness	0.06	0.08	0.15	0.20
T1	Overall Taped Package Thickness	—	0.0567	—	1.44
T2	Carrier Strip Thickness	0.014	0.027	0.35	0.65
W	Carrier Strip Width	0.6889	0.7481	17.5	19
W1	Adhesive Tape Width	0.2165	0.2841	5.5	6.3
W2	Adhesive Tape Position	.0059	0.01968	.15	0.5



NOTES:

1. Maximum alignment deviation between leads not to be greater than 0.2 mm.
2. Defective components shall be clipped from the carrier tape such that the remaining protrusion (L) does not exceed a maximum of 11 mm.
3. Component lead to tape adhesion must meet the pull test requirements.
4. Maximum non-cumulative variation between tape feed holes shall not exceed 1 mm in 20 pitches.
5. Holddown tape not to extend beyond the edge(s) of carrier tape and there shall be no exposure of adhesive.
6. No more than 1 consecutive missing component is permitted.
7. A tape trailer and leader, having at least three feed holes is required before the first and after the last component.
8. Splices will not interfere with the sprocket feed holes.

MCR100 Series

PACKAGE DIMENSIONS

TO-92 (TO-226)
CASE 029-11
ISSUE AL



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.175	0.205	4.45	5.20
B	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
H	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500	---	12.70	---
L	0.250	---	6.35	---
N	0.080	0.105	2.04	2.66
P	---	0.100	---	2.54
R	0.115	---	2.93	---
V	0.135	---	3.43	---

STYLE 10:

1. CATHODE
2. GATE
3. ANODE

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 61312, Phoenix, Arizona 85062-1312 USA
Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada
Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051
Phone: 81-3-5773-3850

ON Semiconductor Website: <http://onsemi.com>

Order Literature: <http://www.onsemi.com/litorder>

For additional information, please contact your
local Sales Representative.