

PTSM 0,5/ 7-P-2,5

Order No.: 1778887



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1778887>

Plug component, Nominal current: 6 A, Rated voltage (III/2): 160 V,
Number of positions: 7, Pitch: 2.5 mm, Connection method: Spring-
cage conn., Color: black, Metal surface: Sn

Commercial data

GTIN (EAN)	
sales group	E410
Pack	100 pcs.
Customs tariff	85369010
Catalog page information	Page 183 (NTK-2010)

Product notes

WEEE/RoHS-compliant since:
09/17/2009



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions / positions

Pitch	2.5 mm
Dimension a	15 mm
Number of positions	7

Technical data

Range of articles	PTSM 0,5/...-P
Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/2)	160 V
Rated voltage (II/2)	320 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	6 A
Nominal voltage U_N	100 V
Nominal cross section	0.5 mm ²
Maximum load current	6 A
Insulating material	PA
Inflammability class acc. to UL 94	V0
Stripping length	6 mm
Nominal voltage, UL/CUL Use Group B	150 V
Nominal current, UL/CUL Use Group B	5 A

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	0.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	0.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	20
Minimum AWG according to UL/CUL	26
Maximum AWG according to UL/CUL	20

Certificates / Approvals



Item	Designation	Description
------	-------------	-------------

1205202	SZS 0,4X2,0	Micro screwdriver, bladed, size: 0.4 x 2.0 x 60 mm, 2-component grip, with non-slip grip and twist cap
---------	-------------	--

The technical drawing shows two views of the 6000 series ball bearing:

- Cross-section view (left):** Shows the internal components including the balls and cage. Dimensions are: outer diameter 15 mm, inner diameter 5 mm, and width 4.5 mm.
- Side view (right):** Shows the profile of the bearing with three balls visible. Dimensions are: total height 1.5 mm, distance from front face to first ball center 2.5 mm, distance between ball centers labeled as $a + 3.6$, and distance from last ball center to back face labeled as a .

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2011 Phoenix Contact
Technical modifications reserved;