









SLA Series

Miniature Slide Switches

SPECIFICATIONS	FEATURES
Contact ratings: 500 mA at 125 VAC Initial contact resistance: 20 milliohms max. Insulation resistance: 100 megohms min. at 500 VDC Dielectric strength: 500 volts RMS for 1 minute Electrical life: 10,000 cycles min. Operating temperature range: -20°C to +85°C Actuation force: 350g ± 200g Solder heat resistance: 260°C max. for 3 seconds Solvent washing permissible	● Miniature compact size. ● Wash-through open frame construction. ● Panel and p.c. mounting models.
	MATERIALS
	Contacts & terminals: Silver plated brass Frame: Zinc plated steel Actuator: PBT Thermoplastic Base: Phenolic laminated sheet

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE


MODEL NO. SLA1200	1P2T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLA1201	1P2T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLA2200	2P2T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT

MODEL NO.


SLA2201




2P2T



SCHEMATIC



MECHANICAL OUTLINE



P.C. BOARD LAYOUT