



3 POLE M12



WIDOK OD STRONY DRUTOW
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
3	Niebieski	BU
4	Czarny	BK


4 POLE M12



WIDOK OD STRONY DRUTOW
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
2	Biały	WH
3	Niebieski	BU
4	Czarny	BK

5 POLE M12



WIDOK OD STRONY DRUTOW
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
2	Biały	WH
3	Niebieski	BU
4	Czarny	BK
5	Szary	GY

PART No MATRIX



W=M12
Ultra-Lock



0=Portable



3=3 Core
4=4 Core
5=5 Core



07 = Male 90°



See table of cable types



M=Metres
F=Feet





LENGTH
020=2 METRES
050=5 METRES
200=20 METRES



Coupling Nut Material
Blank=Standard
7 = Teflon Coated



Blank=Yellow PUR (Standard)
A=Grey
G=Black



WIDOK OD
STRONY CZOLA
VIEW FROM
FRONT SIDE

TABELA 1
CHART 1

MOLEX PN	WOODHEAD PN	L (mm)	POLE
1200200002	W03007P03M020	2000±25	3 POLE
1200798004	W04007E03M050	5000±25	4 POLE
1200798005	W04007P03M050	5000±25	4 POLE
1200798020	W04007P03M100	10000±50	4 POLE

UWAGI:

1. DŁUGOSC CIECIA PRZEWODOW I
SPECYFIKACJE NABIJANIA WEDŁUG LISTY CIECIA.

NOTES:

1. FOR WIRES CUTTING LENGTHS AND CRIMPING
SPECYFICATION SEE THE CUTTING LIST.

ORIGINAL RELEASE EC NO: DRWN:MSPIEWAK CHKD: APPR: A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE 1	DESIGN UNITS	FIRST ANGLE PROJECTION ◎ ▢		
				mm	INCH	DRAWN BY M.DABROWSKA	DATE 2008/10/29	TITLE UL.M12-XP-M-90-XXM-PUR				
			4 PLACES	±	±	CHECKED BY	DATE					
			3 PLACES	±	±	APPROVED BY M.WOLSZCZAK						
			2 PLACES	±	±	ANGULAR ± °		DOCUMENT NO. W0X007XXXMXXX		SHEET NO. 1 OF 1		
			1 PLACE	±	±							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART 1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							