





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		T	ECO-13-000901	08MAR2013	MGT	R.P



- 1 0.00076 [0.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [0.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.00130 [0.000050] MIN NICKEL.
- 2 WIRE RANGE: 0.3 – 0.9mm² (22–18 AWG).
- 3 INSULATION RANGE: 1.50–2.39[0.059–0.094] DIA.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 0.00076 [0.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [0.000100] MIN BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.00130 [0.000050] MIN NICKEL.



SECTION A—A
SCALE 20:1



SECTION B—B
SCALE 20:1

5	0.20 [0.008] PH BRZ	1-770904-1
5	0.20 [0.008] BRASS	1-770904-0
1	0.20 [0.008] PH BRZ	770904-6
PRE-TIN	0.20 [0.008] PH BRZ	770904-4
1	0.20 [0.008] BRASS	770904-3
PRE-TIN	0.20 [0.008] BRASS	770904-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 17OCT02	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK C. JONES 17OCT02				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 17OCT02	NAME SOCKET, MINI UNIVERSAL MATE-N-LOK(TM)			
0 PLC ± -		PRODUCT SPEC				
1 PLC ± -		APPLICATION SPEC				
2 PLC ± -		—				
3 PLC ± 0.15[0.006]		—				
4 PLC ± -		—				
ANGLES ± 1°		WEIGHT —				
FINISH —		CUSTOMER DRAWING				
		SCALE 10:1	SHEET 1 OF 1		REV T	