



| LOC | DIST | REVISIONS |     |              |           |     |      |
|-----|------|-----------|-----|--------------|-----------|-----|------|
| AD  | 00   | P         | LTR | DESCRIPTION  | DATE      | DWN | APVD |
|     |      |           | 0   | 0G3C-0515-04 | 21JUN2007 | RB  | MM   |

- 1

HOUSING MATERIAL: GLASS-FILLED POLYESTER, COLOR-BLACK
- 2

CONTACT MATERIAL: PHOSPHOR BRONZE
- 3

FINISH: .000015 GOLD,SELECTIVE.



|       |       |       |      |            |             |
|-------|-------|-------|------|------------|-------------|
| 8.402 | 7.956 | 7.644 | .156 | 50         | 4-5583660-8 |
| 8.246 | 7.800 | 7.488 | .156 | 49         | 4-5583660-7 |
| 8.090 | 7.644 | 7.332 | .156 | 48         | 4-5583660-6 |
| 7.934 | 7.488 | 7.176 | .156 | 47         | 4-5583660-5 |
| 7.778 | 7.332 | 7.020 | .156 | 46         | 4-5583660-4 |
| 7.622 | 7.176 | 6.864 | .156 | 45         | 4-5583660-3 |
| 7.466 | 7.020 | 6.708 | .156 | 44         | 4-5583660-2 |
| 7.310 | 6.864 | 6.552 | .156 | 43         | 4-5583660-1 |
| 7.154 | 6.708 | 6.396 | .156 | 42         | 4-5583660-0 |
| 6.998 | 6.552 | 6.240 | .156 | 41         | 3-5583660-9 |
| 6.842 | 6.396 | 6.084 | .156 | 40         | 3-5583660-8 |
| 6.686 | 6.240 | 5.928 | .156 | 39         | 3-5583660-7 |
| 6.530 | 6.084 | 5.772 | .156 | 38         | 3-5583660-6 |
| 6.374 | 5.928 | 5.616 | .156 | 37         | 3-5583660-5 |
| 6.062 | 5.616 | 5.304 | .156 | 35         | 3-5583660-4 |
| 5.906 | 5.460 | 5.148 | .156 | 34         | 3-5583660-3 |
| 5.750 | 5.304 | 4.992 | .156 | 33         | 3-5583660-2 |
| 5.594 | 5.148 | 4.836 | .156 | 32         | 3-5583660-1 |
| 5.438 | 4.992 | 4.680 | .156 | 31         | 3-5583660-0 |
| 5.282 | 4.836 | 4.524 | .156 | 30         | 2-5583660-9 |
| 5.126 | 4.680 | 4.368 | .156 | 29         | 2-5583660-8 |
| 4.970 | 4.524 | 4.212 | .156 | 28         | 2-5583660-7 |
| 4.814 | 4.368 | 4.056 | .156 | 27         | 2-5583660-6 |
| 4.658 | 4.212 | 3.900 | .156 | 26         | 2-5583660-5 |
| 4.502 | 4.056 | 3.744 | .156 | 25         | 2-5583660-4 |
| 4.346 | 3.900 | 3.588 | .156 | 24         | 2-5583660-3 |
| 4.190 | 3.744 | 3.432 | .156 | 23         | 2-5583660-2 |
| 4.034 | 3.588 | 3.276 | .156 | 22         | 2-5583660-1 |
| 3.878 | 3.432 | 3.120 | .156 | 21         | 2-5583715-0 |
| 3.722 | 3.276 | 2.964 | .156 | 20         | 1-5583660-9 |
| 3.566 | 3.120 | 2.808 | .156 | 19         | 1-5583660-8 |
| 3.410 | 2.964 | 2.652 | .156 | 18         | 1-5583660-7 |
| 3.254 | 2.808 | 2.496 | .156 | 17         | 1-5583660-6 |
| 3.098 | 2.652 | 2.340 | .156 | 16         | 1-5583660-5 |
| 2.786 | 2.340 | 2.028 | .156 | 14         | 1-5583660-4 |
| 2.630 | 2.184 | 1.872 | .156 | 13         | 1-5583660-3 |
| 2.474 | 2.028 | 1.716 | .156 | 12         | 1-5583660-2 |
| 2.378 | 1.872 | 1.560 | .156 | 11         | 1-5583660-1 |
| 2.162 | 1.716 | 1.404 | .156 | 10         | 1-5583660-0 |
| 2.006 | 1.560 | 1.248 | .156 | 9          | 5583660-9   |
| 1.850 | 1.404 | 1.092 | .156 | 8          | 5583660-8   |
| 1.694 | 1.248 | .936  | .156 | 7          | 5583660-7   |
| 1.538 | 1.092 | .780  | .156 | 6          | 5583660-6   |
| 1.382 | .936  | .624  | .156 | 5          | 5583660-5   |
| 1.226 | .780  | .468  | .156 | 4          | 5583660-4   |
| 1.070 | .624  | .312  | .156 | 3          | 5583660-3   |
| 2.942 | 2.496 | 2.184 | .156 | 15         | 5583660-2   |
| 6.218 | 5.772 | 5.460 | .156 | 36         | 5583660-1   |
| G     | F     | B     | A    | NO OF POSN | PART NO     |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN  
R BROWN

CHK  
M MILLER

APVD  
M MILLER

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:  
INCHES

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± .005  
4 PLC ± -  
ANGLES ± -  
FINISH

DWN  
R BROWN

CHK  
M MILLER

APVD  
M MILLER

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± .005  
4 PLC ± -  
ANGLES ± -  
FINISH

21JUN2007

21JUN2007

21JUN2007

21JUN2007

21JUN2007

21JUN2007

Tyco Electronics

Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

NAME

ASSEMBLY, TWIN LEAF, .156 C/L .010 X .024

SOLDER TYPE POST, END CAP VERSION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=5583660

-

SCALE

4:1

SHEET

1

OF

2

REV

0

