


## ISORYL SCREWDRIVER SETS

### ▼ ISORYL SCREWDRIVER SETS

▷ NF ISO 2380 -1, -2 ; DIN 5261, 5262, 5264, 5265 ; NF ISO 8764 -1, -2 ; DIN 5260 -1, -2



AS.15

| Icon  | Icon   | Icon  |                                                                     |                                |                                       | Number of screwdrivers | ΔΔ g         |
|-------|--------|-------|---------------------------------------------------------------------|--------------------------------|---------------------------------------|------------------------|--------------|
| AR.J5 | AR.J55 |       | ● AR.3 x 75<br>6,5 x 150                                            | 4 x 100<br>AG.8 x 200          | 5,5 x 100                             | 5                      | 406<br>541   |
|       | AS.2   |       | ● AB.4 x 100<br>10 x 200                                            | 6,5 x 150                      | 8 x 200                               | 4                      | 504          |
|       | AS.4   |       | ● AP.0 x 50<br>3 x 150                                              | 1 x 75<br>4 x 200              | 2 x 100                               | 5                      | 685          |
|       |        | AT.J9 | ● AR.3 x 75<br>● AP.0 x 50<br>○ 84.2 - 2,5 - 3                      | 3,5 x 100<br>1 x 75            | 4 x 100<br>2 x 100                    | 9                      | 300          |
| AJ.3  | AS.15  |       | ● AR.3,5 x 75<br>6,5 x 150                                          | 4 x 100                        | 5,5 x 100                             | 14                     | 1210<br>1460 |
|       |        |       | ● AG.8 x 150<br>● AP.1 x 75<br>● AD.1 x 75<br>● AF (screw starters) | 8E x 200<br>2 x 100<br>2 x 100 | AY.3,5 x 100 VE<br>3 x 150<br>3 x 150 |                        |              |

## ISORYL SCREWDRIVERS FOR SLOTTED HEADS

### ▼ AR FOR SLOTTED HEADS - MACHINED BLADES

- Shank machined for access into recesses.
- Polished chrome finish.

| Icon       | e x A<br>mm | T<br>mm | Ø1 x L1<br>mm | Ø2 x L2<br>mm | L<br>mm | ΔΔ<br>g |
|------------|-------------|---------|---------------|---------------|---------|---------|
| AR.2X40    | 0,4 x 2,0   | 0,2     | 2,0 x 40      | 16,0 x 70     | 110     | 13,5    |
| AR.2,5X50  | 0,4 x 2,5   | 0,2     | 2,5 x 50      | 16,0 x 70     | 120     | 15      |
| AR.2,5X75  | 0,4 x 2,5   | 0,2     | 2,5 x 75      | 16,0 x 70     | 145     | 16      |
| AR.3X75    | 0,5 x 3,0   | 0,3     | 3,0 x 75      | 16,0 x 70     | 145     | 17,5    |
| AR.3,5X75  | 0,6 x 3,5   | 0,4     | 3,5 x 75      | 20,5 x 80     | 155     | 31      |
| AR.3,5X100 | 0,8 x 4,0   | 0,4     | 3,5 x 100     | 20,5 x 80     | 180     | 33      |
| AR.4X100   | 0,8 x 4,0   | 0,5     | 4,0 x 100     | 24,0 x 90     | 190     | 45      |
| AR.4X150   | 0,8 x 4,0   | 0,5     | 4,0 x 150     | 24,0 x 90     | 240     | 50      |
| AR.5,5X100 | 1,0 x 5,5   | 0,6     | 5,5 x 100     | 28,0 x 100    | 200     | 71      |
| AR.5,5X150 | 1,0 x 5,5   | 0,6     | 5,5 x 150     | 28,0 x 100    | 250     | 80      |
| AR.6,5X100 | 1,2 x 6,5   | 0,7     | 6,5 x 100     | 30,0 x 110    | 210     | 102     |
| AR.6,5X150 | 1,2 x 6,5   | 0,7     | 6,5 x 150     | 30,0 x 110    | 260     | 114     |
| AR.8X150   | 1,2 x 8,0   | 0,7     | 8,0 x 150     | 30,0 x 110    | 260     | 141     |

