

Matched N-Channel JFET Pairs

PRODUCT SUMMARY					
Part Number	$V_{GS(off)}$ (V)	$V_{(BR)GSS}$ Min (V)	g_{fs} Min (mS)	I_G Typ (pA)	$ V_{GS1} - V_{GS2} $ Max (mV)
U440	-1 to -6	-25	4.5	-1	10
U441	-1 to -6	-25	4.5	-1	20

FEATURES

- Two-Chip Design
- High Slew Rate
- Low Offset/Drift Voltage
- Low Gate Leakage: 1 pA
- Low Noise
- High CMRR: 85 dB.

BENEFITS

- Minimum Parasitics Ensuring Maximum High-Frequency Performance
- Improved Op Amp Speed, Settling Time Accuracy
- Minimum Input Error/Trimming Requirement
- Insignificant Signal Loss/Error Voltage
- High System Sensitivity
- Minimum Error with Large Input Signal

APPLICATIONS


- Wideband Differential Amps
- High-Speed, Temp-Compensated, Single-Ended Input Amps
- High-Speed Comparators
- Impedance Converters

DESCRIPTION

The U440/441 are matched pairs of JFETs mounted in a single TO-71 package. This two-chip design reduces parasitics and gives better performance at very high frequencies while ensuring extremely tight matching. These devices are an excellent choice for use as wideband differential amplifiers in demanding test and measurement applications.

The hermetically-sealed TO-71 package is available with full military screening per MIL-S-19500 (see Military Information).

For similar products in SO-8 packaging see the SST440/SST441 data sheet. For low-noise options, see the SST/U401 series data sheet. For low-leakage alternatives, see the U421/423 data sheet.



ABSOLUTE MAXIMUM RATINGS

Gate-Drain, Gate-Source Voltage	-25 V
Gate-Gate Voltage	±50 V
Gate Current	50 mA
Lead Temperature ($1/16$ " from case for 10 sec.)	300°C
Storage Temperature	-65 to 200°C

Operating Junction Temperature	-55 to 150°C
Power Dissipation :	Per Side ^a 250 mW
	Total ^b 500 mW

Notes

- a. Derate 2 mW/°C above 25°C
- b. Derate 4 mW/°C above 25°C

SPECIFICATIONS (T _A = 25 °C UNLESS OTHERWISE NOTED)								
Parameter	Symbol	Test Conditions	Typ ^a	Limits				Unit
				U440		U441		
				Min	Max	Min	Max	
Static								
Gate-Source Breakdown Voltage	V _{(BR)GSS}	I _G = -1 μA, V _{DS} = 0 V	-35	-25		-25		V
Gate-Source Cutoff Voltage	V _{GS(off)}	V _{DS} = 10 V, I _D = 1 nA	-3.5	-1	-6	-1	-6	V
Saturation Drain Current ^b	I _{DSS}	V _{DS} = 10 V, V _{GS} = 0 V	15	6	30	6	30	mA
Gate Reverse Current	I _{GSS}	V _{GS} = -15 V, V _{DS} = 0 V						
			T _A = 125 °C	-1		-500		-500
Gate Operating Current	I _G	V _{DG} = 10 V, I _D = 5 mA						
			T _A = 125 °C	-1		-500		-500
Gate-Source Forward Voltage	V _{GS(F)}	I _G = 1 mA, V _{DS} = 0 V	0.7					V
Dynamic								
Common-Source Forward Transconductance	g _{fs}	V _{DS} = 10 V, I _D = 5 mA f = 1 kHz	6	4.5	9	4.5	9	mS
Common-Source Output Conductance	g _{os}		70		200		200	μS
Common-Source Input Capacitance	C _{iss}	V _{DS} = 10 V, I _D = 5 mA f = 1 MHz	3					pF
Common-Source Reverse Transfer Capacitance	C _{rss}		1					
Equivalent Input Noise Voltage	\bar{e}_n	V _{DS} = 10 V, I _D = 5 mA f = 10 kHz	4					nV/ √Hz
Matching								
Differential Gate-Source Voltage	V _{GS1} - V _{GS2}	V _{DG} = 10 V, I _D = 5 mA	6		10		20	mV
Gate-Source Voltage Differential Change with Temperature	$\frac{\Delta V_{GS1} - V_{GS2} }{\Delta T}$	V _{DG} = 10 V, I _D = 5 mA T _A = -55 to 125 °C	20					μV/°C
Saturation Drain Current Ratio ^c	$\frac{I_{DSS1}}{I_{DSS2}}$	V _{DS} = 10 V, V _{GS} = 0 V	0.97					
Transconductance Ratio ^c	$\frac{g_{fs1}}{g_{fs2}}$	V _{DS} = 10 V, I _D = 5 mA f = 1 kHz	0.97					
Common Mode Rejection Ratio	CMRR	V _{DG} = 5 to 10 V, I _D = 5 mA	85					dB

Notes


- a. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
- b. Pulse test: PW ≤ 300 μs duty cycle ≤ 3%.
- c. Assumes smaller value in the numerator.

NZFD




TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)


Drain Current and Transconductance vs. Gate-Source Cutoff Voltage




Gate Leakage Current




Output Characteristics




Output Characteristics









Output Characteristics



Output Characteristics




TYPICAL CHARACTERISTICS (T_A = 25°C UNLESS OTHERWISE NOTED)






TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)


Common-Source Input Capacitance vs. Gate-Source Voltage




Common-Source Reverse Feedback Capacitance vs. Gate-Source Voltage




Input Admittance




Forward Admittance







Reverse Admittance



Output Admittance



TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.