


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	MATERIAL	MARKER SIZE	LABELS PER SHEET	SHEETS PER PKG.	STANDARD PKG. QTY.
C150X075YJJ	GMY	1.500 x 0.750	60	42	2500

NOTES:

- .06" CORNER RADIUS ON ALL OUTSIDE CORNERS EXCEPT AS NOTED.
- SHEET AT 8.50".
- PACKAGE IN 1510A BAG. SEE TABLE FOR QUANTITY.

CAD FILENAME/LAYERS: I00472G0_C10247_C150X075YJJ_00.prt

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
1	5/2/07	RVU		ADDED "INKJET" ON HEADER.	4971	R		
0	9-30-04	RVU		DRAWING RELEASED.	0000	R		

PANDUIT CORP TINLEY PARK, ILLINOIS	
OPTIMUM C150X075YJJ LASER/INKJET LABELS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (XXX) ± .005 (.XX) ± .015 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
DRAWN BY RVU	MAT'L: SEE TABLE
DATE 9-30-04	SCALE NTS
CHK'D	DWG C10247 B SIZE